

METERS WITH CONNECTIONS



Take The Power of Connections™ to the next level with Southwire's new line of smart meters.

- Connect to your smartphone via Bluetooth® interface to take measurements and modify meter settings from a safe distance with Southwire's MAPP™ mobile app.
- Record, save and share measurements, add photos and descriptions
- Communicate critical equipment issues via email to get systems back online quickly.



METERS



Southwire™

TOOLS & EQUIPMENT

1-855-SWTOOLS
(855-798-6657)

SOUTHWIRETOOLS.COM

**[BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.]**

©2015 Southwire Company, LLC. All rights reserved.
* Registered Trademark and ™ Trademark of Southwire Company, LLC.



Offering a new way to view and save readings, Southwire's new **MApp™** mobile app lets you monitor your meter from a safe distance. The app includes a trend chart for spotting reading fluctuations and a pop-up menu for modifying meter settings.

Use the app to set up a recording session. Add photos and notes to create a report. Communicate critical maintenance issues via e-mail to get systems back online quickly.



View readings and set up recording sessions right from your mobile phone



Add photos and notes to create a detailed report



Pull-up menu to modify meter settings remotely



E-mail critical equipment issues to maintenance team

15190T

MaintenancePRO™ Color Screen Multimeter

- Bluetooth® interface for downloading, viewing, and sharing on Southwire's MApp™ mobile app.
- On-board memory allows datalogging even when Bluetooth wireless is not connected
- Hi-res color display with graphing and intuitive menu
- Rugged meter with CAT IV 600V / CAT III 1000V



- Bluetooth® interface for downloading, viewing, and sharing on mobile devices



- Intuitive menu - start recordings, view saved measurements and recordings, or change meter settings



- Graphical display shows trends and peaks on recordings



- Recordings and measurements are stored in on-board memory



- Use the SAVE function to save a screen shot of a measurement

23090T

MaintenancePRO™ Smart 1000A Clamp Meter

View, save, store and share measurements and recordings with Southwire's MApp™ mobile app.

Take measurements and modify meter settings from a safe distance

Inrush function captures motor start-up current

Precision TrueRMS meter with 50,000-count display

CAT IV 600V, CAT III 1000V



- Bluetooth® interface for downloading, viewing, and sharing on mobile devices
- High resolution 50,000 count backlit display

23070T / 23030T

MaintenancePRO™ 1000A Clamp Meters

With 11 measuring functions and three current ranges up to 1000A, MaintenancePRO™ clamp meters have the performance to keep systems running smoothly. Measurements are shown on an easy to read 6000 count backlit display. A built-in non-contact AC voltage detector and a powerful LED work light add extra convenience.

The rugged double molded housing and CAT IV 600V / CAT III 1000V safety rating makes these meters suited for tough work environments. They are the perfect choice for the professional electrician.



23030T
1000A AC



23070T
1000A AC/DC