



# Southwire™

## 5" SQUARE BOXES

### 2-7/8" DEEP - WELDED WITH CONDUIT KNOCKOUTS

#### FEATURES

- Combination knockouts allow for greater wiring flexibility

#### APPLICATIONS

- 5" square boxes are used to distribute power to a number of electrical devices where multiple conductor runs are split into two or more directions
- Large cu. in. capacity provides additional space for conductors or devices
- Perfect solution for sensitive bend radius data cable

#### STANDARD MATERIAL

- Galvanized steel

#### CERTIFICATIONS

- UL Listed



5SQBLNK



LISTED

PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM <sup>3</sup> )	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
5SQBLNK*	BLANK, FLAT BOTTOM	67.0 (1097.9)	---	67.0 (1097.9)	10
5SQ5075	FLAT BOTTOM, CONCENTRIC KO'S	67.0 (1097.9)	(12) 1/2" – 3/4"	67.0 (1097.9)	10
5SQ50100	FLAT BOTTOM	67.0 (1097.9)	(4) 1/2" & (8) 1"	67.0 (1097.9)	10
5SQ5075100	FLAT BOTTOM, CONCENTRIC KO'S	67.0 (1097.9)	(4) 1/2" – 3/4", (4) 1/2", (4) 1"	67.0 (1097.9)	10
5SQ100125	FLAT BOTTOM	67.0 (1097.9)	(4) 1" & (4) 1-1/4"	67.0 (1097.9)	10
5SQ50750W	OLD WORK WITH EARS & CLIPS	67.0 (1097.9)	(2) 1/2" & 10 1/2" – 3/4"	67.0 (1097.9)	10

\*Not UL Listed

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



**Southwire™**

# 5" SQUARE BOXES

2-7/8" DEEP - WELDED WITH CONDUIT KNOCKOUTS



5SQ5075



5SQ50100



5SQ5075100



5SQ100125



5SQ50750W

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.