



CIRCUIT DEFENDER™ CIRCUIT INTEGRITY CABLE

Circuit Defender™ cables have been qualified and listed to the demanding requirements of UL 2196 and CAN/ULC-S139 test for fire resistive cables, and are UL listed types FPLR/CMR and CSA Certified FAS. Circuit Defender™ cables meet various industry code requirements (NFPA 70, NFPA 101, NFPA 130, and NFPA 502) for fire resistance according to UL 2196 when selected and installed per applicable codes including federal, state, and local and municipal rules, laws and regulations.

SPECIFICATIONS:

- UL Electrical Circuit Integrity System #44 (FHIT/7 44)--- 2 HR RATED
- UL 1424 Listed FPLR
- UL 444 Listed CMR
- CSA C22.2 No.208 FAS
- UL 2196 and CAN/ULC-S139
- NFPA 70, NFPA 101, NFPA 130, and NFPA 502
- Circuit Defender™ Cables are 2HR fire-resistant and comply with UL 2196 and NFPA fire resistance standards
- UL Listed File #E75610 & #E118871
- CSA Certified LL90458
- Directive (EU) 2015/863 – RoHS 3



LEARN MORE



UNSHIELDED

	Circuit Defender™ FACI 18/2 OFHC N/S FPLR/ CMR or FAS	Circuit Defender™ FACI 16/2 OFHC N/S FPLR/ CMR or FAS	Circuit Defender™ FACI 14/2 OFHC N/S FPLR/
STOCK #	SC4001-2F	SC5001-2F	SC6001-2F
UPC	32886747151	32886747144	32886747137
DESCRIPTION	FACI 18/2 OFHC N/S FPLR/CMR or FAS OR	FACI 16/2 OFHC N/S FPLR/CMR or FAS OR	FACI 14/2 OFHC N/S FPLR/CMR or FAS OR
STOCK # LSZH JACKET	SC4003-2F	SC5003-2F	SC6003-2F

SHIELDED

	Circuit Defender™ Shielded FACI 18/2 OFHC OAS FPLR/CMR or FAS	Circuit Defender™ Shielded FACI 16/2 OFHC OAS FPLR/CMR or FAS	Circuit Defender™ Shielded FACI 14/2 OFHC OAS FPLR/CMR or FAS
STOCK #	SC4002-2F	SC5002-2F	SC6002-2F
UPC	032886442018	032886442025	032886442032
DESCRIPTION	FACI 18/2 OFHC OAS FPLR/CMR or FAS OR	FACI 16/2 OFHC OAS FPLR/CMR or FAS OR	FACI 14/2 OFHC OAS FPLR/CMR or FAS OR