



**Southwire™**

# 4-11/16" SQUARE BOXES

## 3" DEEP - WELDED WITH CONDUIT KNOCKOUTS

### FEATURES

- Combination knockouts allow for greater wiring flexibility
- 3" depth allows for additional wiring capacity

### APPLICATIONS

- 4-11/16" square boxes are used to distribute power to a number of electrical devices where multiple conductor runs are split into two or more directions

### STANDARD MATERIAL

- Galvanized steel

### CERTIFICATIONS

- UL Listed



72181-BLNK



PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM <sup>3</sup> )	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
72181-BLNK*	BLANK	---	---	60.0 (983.3)	25
72181-3/4	RAISED GROUND	(12) 3/4"	(2) 1/2", (2) 3/4"	60.0 (983.3)	25
72181-S	RAISED GROUND, CONCENTRIC KO'S	(6) 1/2", (6) 1/2" - 3/4"	(2) 1/2", (2) 3/4"	60.0 (983.3)	25
72181-1	RAISED GROUND	(8) 1"	(2) 1/2", (2) 3/4"	60.0 (983.3)	25
72181-1-1/4	RAISED GROUND	(8) 1-1/4"	(2) 1/2", (2) 3/4"	60.0 (983.3)	20
72181-1-1/2	RAISED GROUND	(4) 1-1/2"	(2) 1/2", (2) 3/4"	60.0 (983.3)	20

\*Not UL Listed

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.

Job Name/Title: \_\_\_\_\_

Model #: \_\_\_\_\_

Contractor: \_\_\_\_\_



**Southwire™**

## **4-11/16" SQUARE BOXES**

3" DEEP - WELDED WITH CONDUIT KNOCKOUTS



72181-S



72181-1



72181-1-1/4



72181-1-1/2

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.