



Southwire™

PREFAB LED LANTERNS

Southwire Prefab lanterns come in 4 different lumen models, each model has a custom wiring terminal allowing you to add your own cords to fit your specific needs, when wiring you can use the provided strain relief connectors or the 1/2" threaded hubs designed to fit other Southwire fittings. Each model includes a retractable handle for ceiling mounting and low-profile stacking.

- Custom Wiring Terminal - Cord Free
- Accepts 12 gauge through 16 gauge SO Cord
- 1/2" Threaded Hub for Southwire Fittings
- Accepts most sizes of Romex® Brand and MC cable when used with correct fitting
- Includes steel 2x strain relief connectors
- Retractable hanging clip for low profile
- Stackable design
- Replaceable fixture head & wiring terminal
- 5000K CCT

120V - 277VAC 50/60 HZ

CUSTOM WIRING TERMINAL BLOCK

**2 IN 1 DIMMER
(150W & 200W MODELS)**

**OUTDOOR WEATHER RATED (WHEN
USED WITH WEATHERPROOF
CONNECTORS)**

T90060



T90100




T90150



T90200



**WIRING
TERMINAL**



MODEL #	UPC	DESCRIPTION	LUMENS	HEIGHT	WIDTH	LENGTH	WEIGHT
T90060	032886286100	60W PreFab LED Lantern	7,600	10.44"	6.5"	6.5"	6 lbs.
T90100	032886286117	100W PreFab LED Lantern	13,700	11.44"	6.5"	6.5"	6.5 lbs.
T90150	032886286124	150W PreFab LED Lantern	20,500	12.54"	6.5"	6.5"	7 lbs.
T90200	032886286131	200W PreFab LED Lantern	29,500	15.88"	6.5"	6.5"	7.5 lbs.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2022 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

HANGING & FITTING ACCESSORIES

Job sites are complex and having the right product can save you time and money, below you will find a list of Southwire products that are popular with our lanterns.



SC5075HF



CPMH1



JC-100



JHK-32MAG



JHK-64



MCG-50A560



L-42-1

MODEL #	DESCRIPTION	FUNCTION
TEMPORARY LIGHTING MOUNTING ACCESSORIES		
SC-5075HF	4" Square Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications
SC-507HFR	4" Round Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications
SC-507511BHF	4-11/16" Round Swivel Fixture Hanger Ring, with Hands Free Door	Provides a threaded mounting point for the fixture hook and convenient hands free door for direct wire applications
CPMH1	Cage Light Fixture Hook with Threaded End	Pairs with swivel fixture hangers to provide a hanging surface for the light
JC-100	Zinc Fixture Support #12, 100'	Support light fixtures
JHK-32MAG	2" J Hook with 90 lb. Magnet	Supporting and managing string light or extension cord cables
JHK-64	2" J Hook with Mounting Hole	Supporting and managing string light or extension cord cables
JHK-32-AB	2" J Hook with Angled Bracket with Mounting Hole	Supporting and managing string light or extension cord cables
58299040	14" Reusable Cable Ties, Black, 15 Pack	Manage cables and hang small fixtures
58298740	14" Reusable Cable Ties, Black, 100 Pack	Manage cables and hang small fixtures
MCG-50A560	1/2" Cord Grip Steel	Connects and secures power supply to fixture.
CONNECTORS		
BXCN50	1/2 in. Set Screw Connector for BX/MC Cable	Connects and secures power supply to fixture.
L-42-1	1/2" Squeeze Box Connector Straight Zinc	Connects and secures power supply to fixture.
L-41-1	1/2" Squeeze Box Connector Straight Zinc	Connects and secures power supply to fixture.
L-48-1	1/2" Flex Set Screw Box Connector Zinc	Connects and secures power supply to fixture.
MDB-50B	1/2" Double Bite Saddle Box Connector Straight Steel	Connects and secures power supply to fixture.
IML-42-1	1/2" Flex/MC/AC Straight Squeeze Box Connectors, Insulated	Connects and secures power supply to fixture.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2022 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.