



Southwire™

RIGID REDUCING BUSHINGS

316 STAINLESS STEEL

FEATURES

- Threaded NPSM for Rigid and IMC conduit

APPLICATIONS

- Dry location use only
- Use to reduce the entry size of a run of threaded conduit

STANDARD MATERIAL

- Machined 316 stainless steel

CERTIFICATIONS

- UL Listed



RB-5038-SS



PART #	SIZE	MASTER QTY.
RB-5038-SS	1/2" x 3/8"	100
RB-7550-SS	3/4" x 1/2"	50
RB-10050-SS	1" x 1/2"	50
RB-10075-SS	1" x 3/4"	50
RB-12550-SS	1-1/4" x 1/2"	20
RB-12575-SS	1-1/4" x 3/4"	20
RB-125100-SS	1-1/4" x 1"	20
RB-15050-SS	1-1/2" x 1/2"	10
RB-15075-SS	1-1/2" x 3/4"	10
RB-150100-SS	1-1/2" x 1"	10
RB-150125-SS	1-1/2" x 1-1/4"	10
RB-20050-SS	2" x 1/2"	10
RB-20075-SS	2" x 3/4"	10
RB-200100-SS	2" x 1"	10
RB-200125-SS	2" x 1-1/4"	10
RB-200150-SS	2" x 1-1/2"	10
RB-25050-SS	2-1/2" x 1/2"	5
RB-25075-SS	2-1/2" x 3/4"	5

PART #	SIZE	MASTER QTY.
RB-250100-SS	2-1/2" x 1"	5
RB-250125-SS	2-1/2" x 1-1/4"	5
RB-250150-SS	2-1/2" x 1-1/2"	5
RB-250200-SS	2-1/2" x 2"	5
RB-300100-SS	3" x 1"	1
RB-300125-SS	3" x 1-1/4"	1
RB-300150-SS	3" x 1-1/2"	1
RB-300200-SS	3" x 2"	1
RB-300250-SS	3" x 2-1/2"	1
RB-350200-SS	3-1/2" x 2"	1
RB-350250-SS	3-1/2" x 2-1/2"	1
RB-350300-SS	3-1/2" x 3"	1
RB-400200-SS	4" x 2"	1
RB-400250-SS	4" x 2-1/2"	1
RB-400300-SS	4" x 3"	1
RB-400350-SS	4" x 3-1/2"	1
RB-500400-SS	5" x 4"	1
RB-600500-SS	6" x 5"	1

Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.