



Southwire™

4-11/16" SQUARE BOXES

2-1/8" DEEP - WELDED WITH CONDUIT KNOCKOUTS

FEATURES

- Combination knockouts allow for greater wiring flexibility

APPLICATIONS

- 4-11/16" square boxes are used to distribute power to a number of electrical devices where multiple conductor runs are split into two or more directions

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- UL Listed



72171-SW



PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
72171-BLNKW*	BLANK	---	---	42.0 (688.2)	25
72171-1/2W	RAISED GROUND	(12) 1/2"	(2) 1/2", (2) 3/4"	42.0 (688.2)	25
72171-3/4W	RAISED GROUND	(12) 3/4"	(2) 1/2", (2) 3/4"	42.0 (688.2)	25
72171-3/4-1W	RAISED GROUND	(6) 3/4", (4) 1"	(2) 1/2", (2) 3/4"	42.0 (688.2)	25
72171-1W	RAISED GROUND	(8) 1"	(2) 1/2", (2) 3/4"	42.0 (688.2)	25
72171-SW	RAISED GROUND, CONCENTRIC KO'S	(2) 1/2", (10) 1/2"-3/4"	(2) 1/2", (2) 3/4"	42.0 (688.2)	25
72171-1-1/4W	RAISED GROUND	(4) 1-1/4", (4) 1"	(2) 1/2", (2) 3/4"	42.0 (688.2)	25
72171-SWPT	RAISED GROUND, 10/32 GROUND SCREW & 7-1/2" PIGTAIL	(12) 1/2" & 3/4" ECC	(2) 1/2", (2) 1/2" & 3/4" ECC	42.0(688.2)	20

*Not UL Listed

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

4-11/16" SQUARE BOXES

2-1/8" DEEP - WELDED WITH CONDUIT KNOCKOUTS



72171-1/2W



72171-3/4W



72171-3/4-1W



72171-BLNKW



72171-1W



72171-1-1/4W



72171-SWPT

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.