





Southwire®

SUMNER*

WELDING HAND TOOLS CATALOG



SOUTHWIRE.COM

**Trademark of Sumner Manufacturing Co., LLC. Registered in the U.S.
Copyright © Sumner Manufacturing Co., LLC*

OUR STORY

Sumner, a Southwire Company, is a recognized leading manufacturer of material lifts, jack stands, welding tools, material carts and other tools and equipment for the construction market. We are a key supplier to the welding and mechanical contracting industries and have a market presence in more than 50 countries around the world. We maintain manufacturing and sales operations in Texas, Canada, China, the United Kingdom and the Netherlands.

Founded in 1965, our operations began to meet the need for good welding tools and lifting equipment to make pipe installations easier and safer. Early success in the business led the way for us to continually meet the needs of a wide variety of contractors, and we continue to provide a range of equipment options that promote safety and efficiency on the jobsite.

WELDING HAND TOOLS

At Sumner Manufacturing, our welding customers are very important to us. One of our primary goals as a manufacturer is to provide our customers with high quality, competitively priced tools. We learn from welders in the field what products are needed to make their jobs easier. These ideas help us to design and build new and better products. In essence, our customers are part of our Research & Development department, and without their input, we would be unable to continually offer great new products.

Another important part of our philosophy at Sumner is our commitment to safety. All Sumner employees are dedicated to the safety of the individuals who use our products. We understand that price is always a concern to our users, but we will never sacrifice quality or safety just to save costs. We know the demands expected of all Sumner products, and each is built for years of use. It could be said that Sumner tools are built the way the welder would make them. As a result, our tools are not only considered the best in the market, but also the most reliable to get the job done efficiently and safely.

TABLE OF CONTENTS

CURVED LOCKING PLIERS

4" Curved Locking Pliers w/ Cutter	5
5" Curved Locking Pliers w/ Cutter	5
7" Curved Locking Pliers w/ Cutter	5
10" Curved Locking Pliers w/ Cutter	5

STRAIGHT JAW LOCKING PLIERS

7" Straight Jaw Locking Pliers	6
10" Straight Jaw Locking Pliers	6

OTHER PLIERS

MIG Pliers	7
------------------	---

LOCKING CLAMPS

6" Locking Clamp	8
11" Locking Clamp	8
18" Locking Clamp	8
18" Deep Reach Locking Clamp	8

LOCKING CLAMPS W/ SWIVEL PADS

6" Locking Clamp with Swivel Pads	9
9" Locking Clamp with Swivel Pads	9
11" Locking Clamp with Swivel Pads	9
18" Locking Clamp with Swivel Pads	9

OTHER LOCKING TOOLS

Locking Welding Clamp	10
Locking Chain Clamp	11
Locking Sheet Metal Tool	12

CHIPPING HAMMERS

Chipping Hammer	13
Chipping Hammer w/ Wire Brush	14

WIRE BRUSHES

Brass Wire Brush	14
Steel Wire Brush	14

GROUND CLAMPS

200 Amp Copper Ground Clamp	15
500 Amp Steel Ground Clamp	15

OTHER WELDING TOOLS

F Clamp	16
Combination Square	17

These products come with a limited product warranty. For more information please visit: <https://www.southwire.com/resources/warranties>.

WELDING HAND TOOLS

At Sumner Manufacturing, our welding customers are very important to us. One of our primary goals as a manufacturer is to provide our customers with high quality, competitively priced tools. We learn from welders in the field what products are needed to make their jobs easier. These ideas help us to design and build new and better products. In essence, our customers are part of our Research & Development department, and without their input, we would be unable to continually offer great new products.



WELDING HAND TOOLS

CURVED LOCKING PLIERS



CLP4W

Perfect for gripping and torquing various surface shapes, including round pipes, square or hex bolts, and more.

- Curved jaw with hardened teeth to grip a variety of shapes from any angle
- Trigger release for maximum locking force
- Includes wire cutter
- Constructed of high-grade heat-treated alloy steel for durability



CLP5W



CLP7W



CLP10W

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781612	4" Curved Locking Pliers with Cutter	CLP4W	661165816129	4.33"	0.4"	1.37"	0.2 lbs	12
781615	5" Curved Locking Pliers with Cutter	CLP5W	661165816150	5.51"	0.4"	1.57"	0.34 lbs	12
781614	7" Curved Locking Pliers with Cutter	CLP7W	661165816143	7.08"	0.79"	2.36"	0.7 lbs	6
781613	10" Curved Locking Plier with Cutter	CLP10W	661165816136	9.05"	1"	2.36"	1.11 lbs	6

WELDING HAND TOOLS

STRAIGHT JAW LOCKING PLIERS



SLP7

Straight jaw pliers with heavy-duty jaws offer maximum grip on flat or square surfaces.

- Straight jaw with hardened teeth to grip a variety of shapes from any angle
- Trigger release for maximum locking force
- Includes wire cutter
- Constructed of high-grade heat-treated alloy steel for durability



SLP10

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781617	7" Straight Jaw Locking Pliers	SLP7	661165816174	7.08"	0.79"	2.36"	0.83 lbs	6
781616	10" Straight Jaw Locking Pliers	SLP10	661165816167	9.06"	1"	2.36"	1.2 lbs	6

WELDING HAND TOOLS

MIG PLIERS



Perfect for spatter removal (inside or outside a nozzle), bushing installation and removal, and wire cutting.

- Specially-designed nose for easy removal of welding spatter
- Induction-hardened cutting edge stays sharp longer
- Multiple jaws for drawing out wire and removing tips and nozzles

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781618	8" MIG Pliers	MIGP8	661165816181	8.46"	0.5"	1.97"	0.66 lbs	12

WELDING HAND TOOLS

LOCKING CLAMPS



Wide-opening jaws provide more flexibility than standard locking clamps.

- Strong rivet connecting arms to prevent joint integrity from being compromised
- Jaw opening capacity provides versatility in clamping a variety of shapes
- Trigger release for maximum locking force
- Constructed of high-grade heat-treated alloy steel for durability
- Stays adjusted for repetitive use



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781621	6" Locking Clamp	LC6	661165816211	7.1"	1"	3.35"	0.46 lbs	6
781619	11" Locking Clamp	LC11	661165816198	10.83"	0.79"	5.51"	1.63 lbs	6
781623	18" Locking Clamp	LC18	661165816235	18.3"	0.79"	5.9"	3 lbs	6
781624	18" Deep Reach Locking Clamp	LCDR18	661165816242	18.3"	0.79"	9.6"	3.15 lbs	6

WELDING HAND TOOLS

LOCKING CLAMPS WITH SWIVEL PADS



LCS6

Swivel pads provide a larger and more stable gripping surface to hold your work securely.

- Strong rivet connecting arms to prevent joint integrity from being compromised
- Jaw opening capacity provides versatility in clamping a variety of shapes
- Trigger release for maximum locking force
- Constructed of high-grade heat-treated alloy steel for durability
- Stays adjusted for repetitive use



LCS9



LCS11



LCS18

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781622	6" Locking Clamp with Swivel Pads	LCS6	661165816228	7.1"	1"	3.35"	0.46 lbs	6
781626	9" Locking Clamp with Swivel Pads	LCS9	661165816266	9.45"	1.18"	4.33"	1.28 lbs	6
781620	11" Locking Clamp with Swivel Pads	LCS11	661165816204	10.83"	0.79"	5.51"	1.63 lbs	6
781625	18" Locking Clamp with Swivel Pads	LCS18	661165816259	18.3"	0.79"	5.9"	3 lbs	6

WELDING HAND TOOLS

LOCKING WELDING CLAMP



The Locking Welding Clamp has U-shaped jaws for high visibility and access.

- Strong rivet connecting arms to prevent joint integrity from being compromised
- Jaw opening capacity provides versatility in clamping a variety of shapes
- Trigger release for maximum locking force
- Constructed of high-grade heat-treated alloy steel for durability
- Stays adjusted for repetitive use

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781627	9" Locking Welding Clamp	LWC9	661165816273	9.06"	2.56"	3.35"	1.21 lbs	6

WELDING HAND TOOLS

LOCKING CHAIN CLAMP



The Locking Chain Clamp holds and locks around any shape or any size of object and adjusts quickly.

- Strong rivet connecting arms to prevent joint integrity from being compromised
- Jaw opening capacity provides versatility in clamping a variety of shapes
- Trigger release for maximum locking force
- Constructed of high-grade heat-treated alloy steel for durability
- Stays adjusted for repetitive use

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781628	20" Locking Chain Clamp	LCCH20	661165816280	17.7"	0.79"	2.4"	1.55 lbs	6

WELDING HAND TOOLS

LOCKING SHEET METAL TOOL



The Locking Sheet Metal tool locks on to flat surfaces with a secure grip.

- Strong rivet connecting arms to prevent joint integrity from being compromised
- Jaw opening capacity provides versatility in clamping a variety of shapes
- Trigger release for maximum locking force
- Constructed of high-grade heat-treated alloy steel for durability
- Stays adjusted for repetitive use

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781629	8" Locking Sheet Metal Tool	LSM8	661165816297	8.07"	2.56"	3.15"	1.1 lbs	6

WELDING HAND TOOLS

CHIPPING HAMMERS



Solid construction yet lightweight, this chipping hammer provides excellent balance and control for precise chipping.

- Forged in one piece for durability
- Ergonomic grip that reduces impact vibration

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781630	Chipping Hammer	CHMR	661165816303	11"	1.38"	6.1"	1.1 lbs	12

WELDING HAND TOOLS

WIRE BRUSHES

WBCH



These wire brushes are comfortable to use and built to last

CHIPPING HAMMER WITH WIRE BRUSH

- Durable hardened head construction for long life
- Replaceable wire brush
- Vibration reducing spring handle

BRASS WIRE BRUSH

- Strong and durable with securely imbedded brass bristles
- Long curved wood handle with pre-drilled hole for hanging
- Will not rust

STEEL WIRE BRUSH

- Durable scratch brush with securely imbedded stainless steel bristles.
- Long curved wood handle with pre-drilled hang hole.

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781631	Chipping Hammer with Wire Brush	WBCH	661165816310	11"	1.38"	6.1"	1.2 lbs	12
781632	Brass Wire Brush	BWB	661165816327	13.8"	1"	1.968"	0.35 lbs	12
781633	Steel Wire Brush	SWB	661165816334	13.8"	1"	1.77"	0.33 lbs	12

BWB



SWB



WELDING HAND TOOLS

GROUND CLAMPS



These ground clamps provide a secure connection between the ground cable and your work piece. Large contact surface provides positive grounding.

500 AMP STEEL GROUND CLAMP

- Rugged and reliable steel lever design
- 500-Amp Capacity

200 AMP COPPER GROUND CLAMP

- Rugged and reliable copper cast design
- Ball point screw secures the welding cable to the ground clamp
- 200-AMP Capacity
- Heavy duty insulated spring

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781634	500 Amp Steel Ground Clamp	SGC500	661165816341	7.48"	1"	3.15"	0.4 lbs	12
781635	200 Amp Copper Ground Clamp	CGC200	661165816358	6.9"	1"	3.1"	0.87 lbs	12

WELDING HAND TOOLS

F CLAMP



Professional grade F-clamp offers smooth adjustment and high clamping capacity.

- Copper-coated steel screw with pivoting pressure cap
- Large 4-3/4" throat depth
- 1000 lb. maximum clamping capacity

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/ DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781637	12" F Clamp	FC12	661165816372	15"	1.38"	7.87"	3.95 lbs	3

WELDING HAND TOOLS

COMBINATION SQUARE



A precise, easy to read, and well-built combination square for professional results every time.

- Hi-Contrast Black precision-etched scales
- Rust proof stainless steel blade

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	LENGTH/DEPTH	WIDTH	WEIGHT	# ITEMS IN MASTER PACK
781636	12" Combination Square	CSQ12	661165816365	12"	0.79"	4.7"	0.13 lbs	6



Southwire®

SUMNER*

WELDING HAND TOOLS CATALOG

GET SOCIAL WITH US:



/SOUTHWIRETOOLS



@SOUTHWIRETOOLS



@SOUTHWIRETOOLS
@SUMNERCO



SOUTHWIRETOOLS



SCAN TO LEARN MORE

WWW.SOUTHWIRE.COM | 1-855-SWTOOLS

SUMNER - U.S. | 281-999-6900

SUMNER - NETHERLANDS | +31 (0) 85 489 0284

SUMNER - CANADA | (519) 653-5300