



PROLIGHT™

XLE SERIES



The Southwire ProLight XLE work light series is the heavy duty answer to the lighting needs of the jobsite. Keep your site safe with these 6500 to 13,000 lumen work lights that are IP65 rated to keep working indoors or out. The 5000K LEDs will keep going for 50,000 hours, even in ambient temperatures from -30° to 120°F. Included as standard is the aluminum housing, tempered glass lens, protective wire cage and steel brackets. Pros can pick the configuration most appropriate for their application by selecting from single or dual heads that can include floor stands, tripods, or magnets.

- IP65 rated for indoor or outdoor use
- Integrated cage for LED protection
- Tempered glass lenses
- Ambient temp range -30° to 120°F
- 5,000 Kelvin color temperature
- 50,000 hour LED life

111500

- 6500 lumens
- 50 Watts
- Floor stand included
- 5 foot 18/3 SJTW cord



111505

- 6500 lumens
- 50 Watts
- Single head with Tripod included
- Tripod extends to up to 5 feet high
- 5 foot 18/3 SJTW cord



111507

- 6500 lumens
- 50 Watts
- Floor stand and magnet included
- 5 foot 18/3 cord



111005

- 13,000 lumens
- 100 Watts
- Dual head with Tripod included
- Tripod extends to up to 6 feet high
- 5 foot 18/3 SJTW cord



111000

- 13,000 lumens
- 100 Watts
- Dual head light kit with sled
- 5 foot 18/3 SJTW cord



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**



Southwire™

TOOLS & EQUIPMENT



XLE SERIES

Item #	Description	Item Length	Item Height	Item Width	Mast Pack QTY	Lumens	UPC
111000	ProLight™ XLE Dual Head LED Work Light	48	12	18	1	13,000	786625110002
111005	ProLight™ XLE Series Dual Head LED Work Light w/ HD Tripod	85	38	38	1	13,000	786625110057
111500	ProLight™ XLE Series LED Work Light	13	8	8	4	6,500	786625115007
111505	ProLight™ XLE Series LED Work Light w/ 2-Stage Tripod	73	35	35	1	6,500	786625115052
111507	ProLight™ XLE Series LED Work Light w/ Magnet	13	8	8	1	6,500	786625115076



BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.