



# Southwire™

## 4" OCTAGON BOXES

2-1/8" DEEP - DRAWN WITH CONDUIT KNOCKOUTS, EARS 3-1/2" O.C

### FEATURES

- Combo-head fixture/cover mounting screws

### APPLICATIONS

- Octagon boxes are used to install ceiling and wall lighting fixtures, fans, or convenience outlets and devices. Special application product available in this cover style

### STANDARD MATERIAL

- Galvanized steel or 316 stainless steel

### CERTIFICATIONS

- UL Listed



54171-1/2



PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM <sup>3</sup> )	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
54171-1/2	FLAT BOTTOM	(4) 1/2"	(3) 1/2" & (2) 3/4"	20.0 (327.8)	25
54171-DE	FLAT BOTTOM, 2 ADDITIONAL FIXTURE EARS	(4) 1/2"	(3) 1/2" & (2) 3/4"	20.0 (327.8)	25
54171-OW	OLD WORK WITH EARS & CLIPS	(2) 1/2"	(3) 1/2" & (2) 3/4"	20.0 (327.8)	25
54171-DEOW	OLD WORK WITH EARS & CLIPS, 2 ADDITIONAL FIXTURE EARS	(2) 1/2"	(3) 1/2" & (2) 3/4"	20.0 (327.8)	25
54171-3/4	FLAT BOTTOM	(4) 3/4"	(3) 1/2" & (2) 3/4"	20.0 (327.8)	25
54171-S	CONCENTRIC KO'S, FLAT BOTTOM	(2) 1/2" & (2) 1/2" - 3/4"	(3) 1/2" & (2) 3/4"	20.0 (327.8)	25
54171-BLNK	BLANK, NO KO'S	---	---	21.5 (352.3)	25
54171-1/2BB	BLANK BOTTOM	(4) 1/2"	---	21.5 (352.3)	25
54171-BLNKSS	BLANK, 316 STAINLESS STEEL	---	---	21.5 (352.3)	25
54171-SVTSS	PLENUM, 316 STAINLESS STEEL	(2) 1/2" & (2) 3/4"	(3) 1/2" & (2) 3/4"	21.5 (352.3)	25

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



**Southwire™**

# 4" OCTAGON BOXES

2-1/8" DEEP - DRAWN WITH CONDUIT KNOCKOUTS, EARS 3-1/2" O.C



54171-DE



54171-OW



54171-DEOW



54171-3/4



54171-S



54171-BLNK



54171-1/2BB



54171-BLNKSS



54171-SVTSS

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.