

LED Exit Signs

EDGE-LIT SURFACE MOUNT



Easy to Install Safety Solutions

Topaz's LED Edge-Lit Exit Signs are the ideal safety solution for office, industrial, retail and public places. Always ensure exits are clearly marked, even in the event of a power failure with the built-in 90-minute battery backup. These modern units have a clean look, with clear or mirrored panel and your choice of red or green EXIT letters. Surface mount installation is easy with the included canopy and mounting accessories.

FEATURES

- Meets NFPA 70, NFPA 101, UL924, NEC/OSHA Standards
- Battery backup with accessible test button for 90 minutes of illumination during a power outage
- Clear, single face or mirrored, double face configurations available
- Configurable arrows
- Ceiling, wall, or side mounting capability
- Recessed mount kit sold separately

SUGGESTED APPLICATIONS

- Office, industrial, retail and other public spaces





Job Name/Title: _____ Catalog Number _____

Contractor: _____ Notes: _____

LED Exit Signs EDGE-LIT SURFACE MOUNT

GENERAL SPECIFICATIONS

Input Voltage, Frequency Hz: 120/277V, 60Hz
Emergency Backup: Yes
Emergency Duration / Run Time: 90 minutes
Recharge Time: 24 hours
Recycle Times: 500 cycles
Mounting Height: 7.5 ft to 15 ft
Location Rating: Damp
Ambient Operating Temperature: 50°F to 104°F
Battery Type: 4.8V Ni-Cad¹



Battery Backup Push to Test Button and AC Supply Indicator

Mounting Accessories Included



Configurable Arrows



Sleek Extruded Brushed Aluminum Housing

**6" Letter Height
3/4" Stroke**

ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Lumens / Illuminance	Watts	Input Amps 120/277V	Letter Color	Panel Type	Number of Faces
ESEL/SFS/RCL/B	71095	751338035706	Average 55 cd/m ²	3W	31/14mA	Red	Clear	Single Face
ESEL/DFS/RMR/B	71097	751338035737	Average 55 cd/m ²	3W	31/14mA	Red	Mirrored	Double Face
ESEL/SFS/GCL/B	71099	751338035751	Average 78 cd/m ²	3W	33/15mA	Green	Clear	Single Face
ESEL/DFS/GMR/B	71100	751338035850	Average 75 cd/m ²	3W	33/15mA	Green	Mirrored	Double Face

NOMENCLATURE

Example: ESEL/SFS/RCL/B


ESEL = Exit Sign Edge-Lit / SF = Single Face S = Surface Mount / R = Red CL = Clear / B = Battery Backup
 DF = Double Face G = Green MR = Mirrored

ACCESSORIES (SOLD SEPARATELY)

Catalog Number	Order Code	UPC	Description
ESEL/RMKIT	71103	751338035874	Recessed Mount Kit

PRODUCT DIMENSIONS / LINE DRAWING

Catalog Number	(A)	(B)	(C)	Weight
ESEL/XFS/XXX/B	12.1"	9.7"	1.6"	2.53 Lbs.



NOTES:

¹ On all exit and emergency fixtures the battery will be prorated for 5 years.

Specifications subject to change without prior notice.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

WARNING: Some products included in this specification sheet may be subject to the warning requirements of California's Proposition 65. Please refer to your product packaging for more information.

January 2020