





Southwire™

TOOLS & EQUIPMENT

HEAVY DUTY MOUNTABLE CABLE TIES

Patented Cable Ties Designed with Unique, Integral Mounting Holes Allow for Convenient Mounting with Screws or Nails Without Splitting the Tie Itself. These Ties Offer a Fast, Innovative, and Economical Way to Bundle, Secure and Support Cables.



DURABILITY CERTIFIED

TEMP RANGE
-40°F to 185°F
-40° C TO 85° C

50 & 90 POUND TENSILE STRENGTH OPTIONS

UL 62275 AH-2 PLENUM RATED

UV RESISTANT - RATED FOR INDOOR & OUTDOOR USE
(Releasable Ties for Indoor Use Only)

**8-IN. LONG
2-IN. MAX. BUNDLE**

**11-IN. LONG
3-IN. MAX. BUNDLE**

**14-IN. LONG
4-IN. MAX. BUNDLE**



MODEL #	STOCK #	DESCRIPTION	CASE PACK	UPC
CTD0850.15BK	58298840	15-Pack, Black 8-in Nylon Cable Ties, 50LB Tensile Strength	25	032886929373
CTD1150.15BK	58298940	15-Pack, Black 11-in Nylon Cable Ties, 50LB Tensile Strength	25	032886929380
CTD1450.15BK	58299040	15-Pack, Black 14-in Nylon Cable Ties, 50LB Tensile Strength	25	032886929397
CTD0850.100BK	58298240	100-Pack, Black 8-in Nylon Cable Ties, 50LB Tensile Strength	10	032886929311
CTD1150.100BK	58298340	100-Pack, Black 11-in Nylon Cable Ties, 50LB Tensile Strength	10	032886929328
CTD1450.100BK	58298440	100-Pack, Black 14-in Nylon Cable Ties, 50LB Tensile Strength	10	032886929335
CTS0850R.100RD	59506940	100-Pack, Red 8-in Nylon Cable Ties, Releasable, 50LB Tensile Strength	10	032886954511
CTS1150R.100RD	59507040	100-Pack, Red 11-in Nylon Cable Ties, Releasable, 50LB Tensile Strength	10	032886954535
CTS1450R.100RD	59507140	100-Pack, Red 14-in Nylon Cable Ties, Releasable, 50LB Tensile Strength	10	032886954559
CTD0890.100BK	58298540	100-Pack, Black 8-in Nylon Cable Ties, 90LB Tensile Strength	10	032886929342
CTD1190.100BK	58298640	100-Pack, Black 11-in Nylon Cable Ties, 90LB Tensile Strength	10	032886929359
CTD1490.100BK	58298740	100-Pack, Black 14-in Nylon Cable Ties, 90LB Tensile Strength	10	032886929366

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™ Trademark of Southwire Company, LLC.