



Southwire™

4" SQUARE BOXES

2-1/8" DEEP - DRAWN WITH CONDUIT KNOCKOUTS

FEATURES

- Combination knockouts allow for greater wiring flexibility
- Special application product available in this box/style depth. Reference catalog section starting on page 11-164 for details: Painted Red

APPLICATIONS

- 4" square boxes are used to distribute power to a number of electrical devices where multiple conductor runs are split into two or more directions

STANDARD MATERIAL

- Galvanized steel or 316 stainless steel

CERTIFICATIONS

- UL Listed



52171-1/2DR



PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
52171-1/2DR	FLAT BOTTOM	(12) 1/2"	(4) 1/2"	30.3 (496.5)	25
52171-3/4DR	FLAT BOTTOM	(8) 3/4"	(2) 1/2" & (2) 3/4"	30.3 (496.5)	25
52171-SDR	CONCENTRIC KO'S	(6) 1/2" & (6) 1/2" - 3/4"	(3) 1/2" & (2) 3/4"	30.3 (496.5)	25
52171-1DR	RAISED GROUND	(8) 1"	(2) 1/2" & (2) 3/4"	30.3 (496.5)	25
52171-BLNK	BLANK, NO KO'S	---	---	30.3 (496.5)	25
52171-BLNKSS	BLANK, 316 stainless steel	---	---	30.3 (496.5)	25
52171-1/2-3/4	RAISED GROUND	(8) 1/2" & (4) 3/4"	2) 1/2" & (2) 3/4"	21.0 (344.1)	24

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

4" SQUARE BRACKETED BOXES

1-1/2" DEEP - WELDED WITH CLAMPS



52171-3/4DR



52171-SDR



52171-1DR



52171-BLNK



52171-BLNKSS

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.