



# Southwire™

## PVC RIGID SPECIAL RADIUS ELBOWS

### SCHEDULE 40 PVC

#### FEATURES

- Cleanly finished with plain spigot (plain) ends
- High tensile and impact strength

#### APPLICATION

- Enable connections between straight lengths of pipe; sizes available to accommodate almost any design configuration change

#### STANDARD MATERIAL

- Schedule 40 PVC



1449

PART #	SIZE	MASTER QTY.	WEIGHT/ CASE (LBS.)
1377	1" X 90° X 18"	1	1
1378	1" X 90° X 24"	1	1
1379	1" X 90° X 36"	1	1
1380	1" X 90° X 48"	1	2
1381	1" X 45° X 18"	1	1
1382	1" X 45° X 24"	1	1
1383	1" X 45° X 36"	1	1
1384	1" X 45° X 48"	1	1
1385	1" X 30° X 18"	1	1
1386	1" X 30° X 24"	1	1
1387	1" X 30° X 36"	1	1
1388	1" X 30° X 48"	1	2
1389	1-1/4" X 90° X 18"	1	1
1390	1-1/4" X 90° X 24"	1	1
1391	1-1/4" X 90° X 36"	1	1
1392	1-1/4" X 90° X 48"	1	1
1393	1-1/4" X 45° X 18"	1	1
1394	1-1/4" X 45° X 24"	1	1
1395	1-1/4" X 45° X 36"	1	1
1396	1-1/4" X 45° X 48"	1	1
1397	1-1/4" X 30° X 18"	1	1

PART #	SIZE	MASTER QTY.	WEIGHT/ CASE (LBS.)
1398	1-1/4" X 30° X 24"	1	2
1399	1-1/4" X 30° X 36"	1	2
1400	1-1/4" X 30° X 48"	1	2
1402	1-1/2" X 90° X 24"	1	3
1403	1-1/2" X 90° X 36"	1	3
1404	1-1/2" X 90° X 48"	1	3
1405	1-1/2" X 45° X 18"	1	3
1406	1-1/2" X 45° X 24"	1	3
1407	1-1/2" X 45° X 36"	1	3
1408	1-1/2" X 45° X 48"	1	3
1409	1-1/2" X 30° X 18"	1	3
1410	1-1/2" X 30° X 24"	1	3
1411	1-1/2" X 30° X 36"	1	3
1412	1-1/2" X 30° X 48"	1	3
1413	2" X 90° X 18"	1	1
1414	2" X 90° X 24"	1	1
1415	2" X 90° X 36"	1	2
1416	2" X 90° X 48"	1	2
1417	2" X 45° X 18"	1	2
1418	2" X 45° X 24"	1	2



Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



# Southwire™

## PVC RIGID SPECIAL RADIUS ELBOWS

### SCHEDULE 40 PVC (CONTINUED)

PART #	SIZE	MASTER QTY.	WEIGHT/ CASE (LBS.)
1419	2" X 45° X 36"	1	2
1420	2" X 45° X 48"	1	2
1421	2" X 30° X 18"	1	2
1422	2" X 30° X 24"	1	2
1423	2" X 30° X 36"	1	3
1424	2" X 30° X 48"	1	3
1425	2-1/2" X 90° X 18"	1	4
1426	2-1/2" X 90° X 24"	1	4
1427	2-1/2" X 90° X 36"	1	5
1428	2-1/2" X 90° X 48"	1	5
1429	2-1/2" X 45° X 18"	1	7
1430	2-1/2" X 45° X 24"	1	1
1431	2-1/2" X 45° X 36"	1	2
1432	2-1/2" X 45° X 48"	1	2
1433	2-1/2" X 30° X 18"	1	2
1434	2-1/2" X 30° X 24"	1	1
1435	2-1/2" X 30° X 36"	1	3
1436	2-1/2" X 30° X 48"	1	1
1437	3" X 90° X 18"	1	2
1438	3" X 90° X 24"	1	1
1439	3" X 90° X 36"	1	2
1440	3" X 90° X 48"	1	2
1441	3" X 45° X 18"	1	4
1442	3" X 45° X 24"	1	5
1443	3" X 45° X 36"	1	6
1444	3" X 45° X 48"	1	7
1445	3" X 30° X 18"	1	8
1446	3" X 30° X 24"	1	8
1447	3" X 30° X 36"	1	9
1448	3" X 30° X 48"	1	9

PART #	SIZE	MASTER QTY.	WEIGHT/ CASE (LBS.)
1449	3-1/2" X 90° X 24"	1	4
1450	3-1/2" X 90° X 36"	1	4
1451	3-1/2" X 90° X 48"	1	2
1452	3-1/2" X 45° X 24"	1	5
1453	3-1/2" X 45° X 36"	1	3
1454	3-1/2" X 45° X 48"	1	4
1455	3-1/2" X 30° X 24"	1	5
1456	3-1/2" X 30° X 36"	1	6
1457	3-1/2" X 30° X 48"	1	8
1458	4" X 90° X 24"	1	9
1459	4" X 90° X 36"	1	12
1460	4" X 90° X 48"	1	11
1461	4" X 45° X 24"	1	15
1462	4 X 45 X 36	1	3
1463	4" X 45° X 48"	1	4
1464	4" X 30° X 24"	1	5
1465	4" X 30° X 36"	1	7
1466	4" X 30° X 48"	1	3
1467	5" X 90° X 36"	1	3
1468	5" X 90° X 48"	1	4
1469	5" X 45° X 36"	1	4
1470	5" X 45° X 48"	1	7
1471	5" X 30° X 36"	1	11
1472	5" X 30° X 48"	1	11
1473	6" X 90° X 36"	1	5
1474	6" X 90° X 48"	1	5
1475	6" X 45° X 36"	1	5
1476	6" X 45° X 48"	1	6
1477	6" X 30° X 36"	1	6
1478	6" X 30° X 48"	1	6



1449



Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.