



LED MINI-REFLECTORS

5 WATT GU10 SERIES

SUGGESTED APPLICATIONS

- Ideal for track lighting

FEATURES

- Supports California Title 20 compliance
- No mercury
- Up to 90% energy savings
- Last up to 10x longer than incandescent
- Dims down to 10% total light output*



INPUT VOLTAGE: 120V

FREQUENCY: 60Hz

DIMMABLE: 100% TO 10%

EFFICACY: UP TO 81 LPW


CRI: 93

MOD: 2"

BEAM ANGLE: 40°

**LIFETIME (L70):
UP TO 25,000 HOURS**

**-40°F MINIMUM START
TEMPERATURE**



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



LED MINI-REFLECTORS

5 WATT GU10 SERIES

ITEM SPECIFICATIONS | ORDER INFO

MODEL #	ORDER CODE	UPC	LUMENS	WATTAGE	CCT	CBCP (CD) MOL	MOL	M.O.L. (INC PINS)	T20
LGU10/5/930/D/G7	79418	751338030732	450	5.5W	3000K	642	1.8"	2.05"	YES
LGU10/5/940/D/G7	79419	751338030749	450	5.5W	4000K	607	1.8"	2.05"	YES
LGU10/5/950/D/G7	79420	751338030756	450	5.5W	5000K	668	1.8"	2.05"	YES

Not for sale in residential new construction in California.

ORDERING GUIDE

Example: **LGU10/5/930/D/G7**


PRODUCT	WATTAGE	CRI	OPTIONS	GENERATION
LGU10 = L = LED, GU10 = GU10 BASE	5 = 5 WATTS	930 = 90 CRI AND 3000K 940 = 90 CRI AND 4000K 950 = 90 CRI AND 5000K	D = DIMMABLE	G7

ENERGY SAVINGS *Based on 12 hours/day and \$0.11/kWh*

MODEL #	LED WATTAGE	INCANDESCENT REPLACEMENT WATTAGE	WATTS SAVED	YEARLY SAVINGS	5 YEAR SAVINGS
LGU10/5/930/D/G7	5.5W	60W	54.5W	\$26	\$131
LGU10/5/940/D/G7	5.5W	60W	54.5W	\$26	\$131
LGU10/5/950/D/G7	5.5W	60W	54.5W	\$26	\$131

DIMENSIONS | WEIGHT

MODEL #	A (IN)	B (IN)	WEIGHT (LBS.)
LGU10/5/930/D/G7	2.05	2.00	0.1
LGU10/5/940/D/G7	2.05	2.00	0.1
LGU10/5/950/D/G7	2.05	2.00	0.1



NOTES

*Dimming- This product is designed to be compatible with most leading-edge type incandescent and LED style dimmers. (Dimming range 100% down to 10%). Product performance may vary depending on dimmer manufacturer and circuit loading. Visit www.southwire.com or contact your local Southwire representative for a list of compatible dimmers.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications are subject to change without prior notice. Replacement wattage shown depends on application and fixture.



800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.