Southwire®

-GENESIS-

Limited-Energy Cable

Audacious Sound Cable®

DIRECT BURIAL

300V (max) Operating Voltage

-20°C 75°C Operating Temperature

Sunlight Resistant

Direct Burial

RoHS Compliant


cETLus Listed

APPLICATIONS

Genesis Audacious Sound Cable® delivers better quality and bolder sound. Oxygen-free copper conductors and a high strand count deliver minimal distortion for optimal performance.

- In burial applications with or without conduit
- In outdoor locations, exposed to sunlight and moisture

WE'VE GOT IT MADE IN AMERICA™



SPECIFICATIONS

Genesis Audacious Sound Cable® meets or exceeds the following specifications:

- UL 1685 – General Purpose Rated
- UL 444 – Communication Cables, Type CM
- UL 13 – Power-Limited Circuit Cables, Type CL3

CONSTRUCTION

1. **Conductor:** Oxygen-Free Bare Copper conductors for excellent sound transmission and low voltage drop
2. **Insulation:** SRPVC
3. **Rip Cord:** Durable rip cord for efficient jacket stripping and removal
4. **Jacket:** PVC, Countdown® Length Markings for easy tracking of usage and remaining cable

CONDUCTOR COLORS			
1: Black ●	2: Red ●	3: White ○	4: Green ●

Southwire Company, LLC. • One Southwire Drive • Carrollton, GA 30119

©2025 Southwire Company, LLC. All Rights Reserved.
®Registered Trademark & ™Trademark of Southwire Company, LLC.

WE DELIVER POWER... RESPONSIBLY.®

Southwire®

-GENESIS-

Limited-Energy Cable

AUDACIOUS SOUND CABLE®, DIRECT BURIAL

AWG	NUMBER OF CONDUCTORS	SOLID / STRANDED	NOMINAL O.D. (in.)	DC RESISTANCE (Ohms/1000ft. at 20ºC)	CAPACITANCE (pF/ft.)	WEIGHT (lbs./1000ft.)	PRODUCT NUMBER
16	2	65 strand	0.287	4.19	35.2	43.2	5283
16	4	65 strand	0.328	4.19	35.2	68.8	5284
14	2	105 strand	0.319	2.62	40.0	56.9	5285
14	4	105 strand	0.366	2.62	40.0	93.8	5286

SAMPLE PRINT LEGEND

GENESIS AUDACIOUS OXYGEN FREE P/N 528X XC XAWG (ETL) CL3 OR CM C(ETL)US SUN RES DIR BUR 75C
"AUDIO ONLY" (RoHS) W/O #XXXXXX-XXXXXX XXXX FT RM# A B C D E F 1 2 3 4 5 6 7 8 9

Southwire Company, LLC. • One Southwire Drive • Carrollton, GA 30119

©2025 Southwire Company, LLC. All Rights Reserved.
®Registered Trademark & ™Trademark of Southwire Company, LLC.

WE DELIVER POWER... RESPONSIBLY.®