



Southwire™

CONCRETE RINGS

2-1/2" & 3-1/2" DEEP - WITH CONDUIT KNOCKOUTS

FEATURES

- Extra long external mounting tabs allow easy installation by nailing or screwing the boxes to wooden or steel concrete forms
- Knockouts are sealed against box surface to prevent concrete slurry and water from entering the box
- The top covers are removable allowing any before-pour work (sold separately)

APPLICATIONS


- Masonry boxes are used as a junction box or to secure a wiring device in masonry block construction
- 2-1/2" deep boxes are used in 4" block walls, 3-1/2" deep boxes are used in 6" or 8" block walls
- Gangable masonry boxes allow installer to construct a box to hold multiple devices

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- UL Listed



OCR-200



OCR-250



OCR-300



OCR-350




OCR-400



OCR-500



OCR-600



OCR-300341



OCR-350341



OCR-400341



OCR-400FAN

Rev. 2, 11/25

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

CONCRETE RINGS

2-1/2" & 3-1/2" DEEP - WITH CONDUIT KNOCKOUTS

PART #	DESCRIPTION	K.O. PATTERN FIG #	RING DEPTH	KNOCKOUTS	CUBIC INCHES (CM ³)	MASTER QTY.
				SIDE CONDUIT		
OCR-200	1/2" & 3/4" KO'S	1	2"	(4) 1/2" & (4) 3/4"	24.5 (401.4)	10
OCR-250		1	2-1/2"	(4) 1/2" & (4) 3/4"	30.8 (504.7)	10
OCR-300		1	3"	(4) 1/2" & (4) 3/4"	37.0 (606.3)	10
OCR-350		2	3-1/2"	(8) 1/2" & (8) 3/4"	43.0 (704.6)	20
OCR-400		2	4"	(8) 1/2" & (8) 3/4"	49.3 (807.8)	5
OCR-500		2	5"	(8) 1/2" & (8) 3/4"	61.5 (1007.8)	5
OCR-600		2	6"	(8) 1/2" & (8) 3/4"	74.0 (1212.6)	5
OCR-300341	3/4" & 1" KO'S	1	3"	(4) 3/4" & (4) 1"	37.0 (606.3)	10
OCR-350341		1	3-1/2"	(4) 3/4" & (4) 1"	43.0 (704.6)	5
OCR-400341		3	4"	(8) 3/4" & (8) 1"	49.3 (807.8)	5

PART #	DESCRIPTION	RECOMMENDED MAX LOAD RATINGS		KO PATTERN FIG#	KNOCKOUTS	CUBIC INCHES (CM ³)	MASTER QTY.
		CEILING FAN (DYNAMIC) LBS.	FIXTURE (STATIC) LBS.		SIDE CONDUIT		
OCR-400FAN	1/2" & 3/4" KO'S, CEILING FAN/LIGHT FIXTURE SUPPORT	35	75	2	49.3 (807.8)	(8) 1/2" & (8) 3/4"	5

Rev. 2, 11/25

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.