

Job Name/Title: \_\_\_\_\_ Catalog Number \_\_\_\_\_  
 Contractor: \_\_\_\_\_ Notes: \_\_\_\_\_

# LED Linear Lighting

## 42W 8 Ft Double-Ended LED R17d Base Retrofit Frosted T8 with Internal Driver

### Features


- PET-Coated glass tube construction
- Ballast bypass, double-end connection
- Designed for retrofit use in HO fixtures
- Replacement for 8 ft. 86W T8/HO or 110W T12/HO
- Extremely long life and energy efficient
- Contains no mercury

### Specs

- 120-277V
- 82 CRI
- 160° Beam spread
- 50,000 Hours functional life (L70)
- -40° to 105°F Ambient operating temperature

### Applications

- Replacement for linear fluorescent
- Offices, retail, commercial fixtures



Catalog Number	Order Code	UPC	Watts	CCT	Lumens	LPW	Input Amps 120/277V	Case Qty
<b>L8T8B/840/42F/R17D</b>	74538	751338030886	42W	4000K	5,400	129	0.4 / 0.2	10-PK
<b>L8T8B/850/42F/R17D</b>	74539	751338030893	42W	5000K	5,500	131	0.4 / 0.2	10-PK
<b>L8T8B/865/42F/R17D</b>	74540	751338032118	42W	6500K	5,500	131	0.4 / 0.2	10-PK

#### NOTES:

Specifications subject to change without notice

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

**WARNING:** Some products included in this specification sheet may be subject to the warning requirements of California's Proposition 65. Please refer to your product packaging for more information.

