

Contractor:_

Job Name/Title:_____Catalog Number_____

Notes:

LED Round Canopy POWER & CCT SELECTABLE





Contractor-Friendly Canopy

The Topaz Round Canopy is a durable and attractive LED lighting solution for safety and functionality of covered outdoor spaces. Designed with contractorfriendly features, the removable mounting plate ensures a simple and secure installation, while the wattage and CCT selectable switches allow for on-site illumination adjustments. The domed lens is ideal for parking garages where uniformity throughout rows of multiple fixtures is key.

FEATURES

- Choose from three wattages and three CCT choices for up to nine possible configurations
- Removable mounting plate allows for secure, hassle-free installation
- Low-profile designs provides more clearance than traditional canopy fixtures
- Available in bronze and white finishes
- · Ceiling or pendant mount options

APPLICATIONS

- Residential and commercial
- Exterior canopies
- Parking garages
- Stairwells
- Carports





Contractor:

Notes:

LED Round Canopy POWER & CCT SELECTABLE

GENERAL SPECIFICATIONS

Input Voltage, Frequency: 120-277V, 50/60Hz **Power Factor, THD %:** >0.9, <25% Dimmable: 0-10V down to 10%¹ Efficacy: Up to 146 LPW Minimum CRI: 82

Beam Angle: 90° IES Distribution: Type V BUG Rating: B3-U3-G2 Functional Life (L70): 50,000 hours Lens Type: Polycarbonate Location Rating: Wet

IP Rating: IP65 Ambient Operating Temperature: -40°F to 104°F Housing Construction: Aluminum Mounting Options: Ceiling or pendant mount

ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Lumens	Wattage	Input Current @120V/277V	ССТ	Finish/ Color	DLC Premium ID+
CPR-60WPCTS-BZ	72768	751338039971	4,388 5,741 8,329	30W 40W 60W	0.26/0.12A 0.35/0.16A 0.53/0.24A	3000K 4000K 5000K	Bronze	P6A5595I
CPR-60WPCTS-WH	72769	751338039988	4,388 5,741 8,329	30W 40W 60W	0.26/0.12A 0.35/0.16A 0.53/0.24A	3000K 4000K 5000K	White	P6A5595I

NOMENCLATURE

Example: CPR-60WPCTS-BZ CPR = Canopy Round - 60W = 30W/40W/60W P = Power Select CTS = Color Temperature Select 3000K|4000K|5000K - BZ = Bronze WH = White

ENERGY SAVINGS

Catalog Number	LED Wattage	HID Replacement Wattage	Watts Saved	Yearly Savings	5 Year Savings
Based on 12 hours/day and \$0.11/kWh					
CPR-60WPCTS-xx	30W 40W 60W	150W 175W 250W	120W 135W 190W	\$58 \$65 \$92	\$289 \$325 \$458

DIMENSIONS / WEIGHTS

				КО	
Catalog Number	(A)	(B)	Mounting Plate Dimensions	Information	Weight
CPR-60WPCTS-xx	11.85"	4.11"	6.85" x 6.14" x 0.37"	(3) 1⁄2" NPT threaded hubs	5.3 Lbs.



NOTES:

*DLC Primary Use Designation: Outdoor Parking Garage Luminaires

¹Dimming with standard 0-10V control system or wall dimmers. Dimming complies with IEC60929 Annex E. Fixture may not be compatible with all dimmers. Dimming performance may vary based on selected dimmer. Visit www.topaz-usa.com/led-dimmer-compatibility for up-to-date dimmer compatibility information.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications subject to change without prior notice. Replacement wattage shown depends on application and fixture.

WARNING: Some products included in this specification sheet may be subject to the warning requirements of California's Proposition 65. Please refer to your product packaging for more information.



Contractor:_____Notes:_____

LED Round Canopy POWER & CCT SELECTABLE

PHOTOMETRICS

CPR-60WPCTS



	Zonal Flux Summary									
Zone (Deg Vert)	Flux (Lumens)	Percent of Total		Zone (Deg Vert)	Flux (Lumens)	Percent of Total		Zone (Deg Vert)	Flux (Lumens)	Percent of Total
0-10	150.7	1.8%		90-100	160.6	1.9%		0-20	605.8	7.2%
10-20	455.1	5.4%		100-110	47.4	0.6%		0-30	1358	16.2%
20-30	752.5	9.0%		110-120	5.8	0.1%		0-40	2379	28.4%
30-40	1020	12.2%		120-130	2.2	0.0%		0-60	5038	60.1%
40-50	1244	14.8%		130-140	1.9	0.0%		0-80	7692	91.7%
50-60	1415	16.9%		140-150	1.1	0.0%		10-90	8017	95.6%
60-70	1495	17.8%		150-160	0.4	0.0%		20-50	3017	36.0%
70-80	1158	13.8%		160-170	0.0	0.0%		40-90	5789	69.0%
80-90	475.8	5.7%		170-180	0.0	0.0%		60-90	3129	37.3%
0-90	8168	97.4%		90-180	219.6	2.6%		0-180	8387	100.0%

		Ground-level distance to half-of-nadir illuminance (ft	
Height(ft)	Illuminance at Nadir (fc)	0-180 deg	90-270 deg
6.0	43.5	9.49	9.49
8.0	24.5	12.65	12.65
10.0	15.7	15.81	15.81
12.0	10.9	18.97	18.97
14.0	8.0	22.14	22.14
16.0	6.1	25.30	25.30

November 2021