



Southwire™

INSULATED METALLIC GROUNDING BUSHINGS WITH ALUMINUM LAY-IN LUG - MALLEABLE IRON

FEATURES

- Liner is rated flame retardant to 105°C
- UL listed for use with copper or aluminum grounding conductor

APPLICATIONS

- Indoor or outdoor use (aluminum lug)
- Use with locknut to terminate service conduit to a cabinet
- Lug provided for bonding jumper to a neutral bus bar
- Round surface of bushing prevents damage to wire insulation
- Plastic liner prevents damage to wire insulation

STANDARD MATERIAL

- Body - Malleable iron
- Plastic insulator
- Lug - Aluminum
- Clamping screw - Steel
- Set screws - Steel

STANDARD FINISH


- Body - Zinc plated



331M



PART #	SIZE	GROUNDING LUG WIRE SIZE		INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B
		MIN.	MAX.					
331M	1/2"	14	4	50	500	45	1.08"	.57"
332M	3/4"	14	4	50	500	50	1.31"	.57"
333M	1"	14	4	25	250	40	1.61"	.65"
334M	1-1/4"	14	4	20	200	35	1.91"	.71"
334AM	1-1/4"	14	1/0	20	200	35	1.91"	.71"
335M	1-1/2"	14	4	10	100	25	2.16"	.73"
335AM	1-1/2"	14	1/0	10	100	25	2.16"	.73"
336M	2"	14	4	10	100	30	2.72"	.73"
336AM	2"	14	1/0	10	100	30	2.72"	.73"
337M	2-1/2"	14	1/0	---	50	25	3.23"	.94"
337AM	2-1/2"	6	250 MCM	---	50	25	3.23"	.94"
338M	3"	14	1/0	---	25	18	3.88"	.94"
338AM	3"	6	250 MCM	---	25	18	3.88"	.94"
339M	3-1/2"	14	1/0	---	10	20	4.43"	.94"
339AM	3-1/2"	6	250 MCM	---	10	20	4.43"	.94"
340M	4"	14	1/0	---	10	25	4.89"	.94"
340AM	4"	6	250 MCM	---	10	25	4.89"	.94"
340ALM	5"	6	250 MCM	---	10	25	6.10"	1.14"
340BLM	6"	6	250 MCM	---	10	35	7.15"	1.14"



Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.