



Southwire™

RIGID WATERTIGHT HUBS WITH BONDING SCREW - ALUMINUM

FEATURES

- Raintight, oiltight, and dust tight
- Flame-retardant insulated throat
- Oversized locknut protects against damage from vibration and promotes positive grounding

APPLICATION

- Indoor or outdoor use
- Use to connect Rigid or IMC conduit to a load center or other metal enclosure where a watertight joint is required at knockouts or slip-fit holes

STANDARD MATERIAL

- Aluminum

CERTIFICATIONS


- NEMA 2, 3R, 4, 4X, 5, 12, 13



201BAL



PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	MAX. COPPER WIRE SIZE UL#
201BAL	1/2"	25	250	23	1.31"	1.54"	#8
202BAL	3/4"	10	100	13	1.37"	1.73"	#8
203BAL	1"	10	100	19	1.59"	2.04"	#8
204BAL	1-1/4"	2	20	6	1.59"	2.42"	#8
205BAL	1-1/2"	---	20	7	1.59"	2.79"	#8
206BAL	2"	---	10	6	1.59"	3.30"	#8
207BAL	2-1/2"	---	5	3	2.44"	3.70"	#6
208BAL	3"	---	5	5	2.44"	4.39"	#6
209BAL	3-1/2"	---	5	7	2.44"	4.88"	#6
210BAL	4"	---	1	2	2.44"	5.50"	#4



Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.