

SERIES 2600

AXEL, THE BIG LIFT

SUMNER^{*}
A Southwire Company

- ✓ 10 or 15 ft (3 - 4.6 m)
- ✓ 1,100 lb (500 kg) capacity
- ✓ 2 speed winch
- ✓ Travels through doorway
- ✓ Legs fold for compact storage
- ✓ Rolls into vehicles
- ✓ Adjustable steering level handle



Legs unlock with plunger pin and fold up for storage. Roller wheels under each leg for ease of moving lift in stored position.



Rugged two speed winch makes lifting heavy loads a snap.




Aluminum pulleys enclosed to prevent cable from coming off.



Mast roller wheels help to roll lift into vehicles.




Mast hold bar for horizontal transportation. Hold down bar can be reshaped if bent.



Nifty lifting hook for crane use.

SERIES 2600


AXEL, THE BIG LIFT




Adjustable steering handle that pops out of way with push button.



Forks can quickly be reversed with plunger pins.



Outrigger locking mechanism locks legs both in stored or operating position.
Note: Outriggers standard on 15' model, optional on 10' model.



With push of a button, optional fork extensions extend forks extra 8" / 20 cm. Extensions store in forks. Extension capacity 450lb / 205kg.

Technical Data	2610		2615	
Pay Load	1100 lb	500 kg	1100 lb	500 kg
Lifting height - forks down	9' 10"	3.0 m	14' 5"	4.4 m
Lifting height - forks reversed	11' 10"	3.6 m	16' 5"	5.0 m
Length - working	62"	157.5 cm	62"	157.5 cm
Width - working	74.5	189.2 cm	74.5	189.2 cm
Height - working	76"	193 cm	76"	193 cm
Min. load height	4"	10 cm	4"	10 cm
Ground clearance	2.5"	6.4 cm	2.5"	6.4 cm
Length - stowed	34 "	86.4 cm	34 "	86.4 cm
Width - stowed	31.5"	80 cm	31.5"	80 cm
Height - stowed	76.5 "	194.3 cm	76.5 "	194.3 cm
Weight Lift	292 lb	132.5 kg	346 lb	157 kg
10' Safety Brakes	783882			
15' Safety Brakes			783883	
Fork Extension	783163			



For more information visit sumner.com