



Southwire®

21010N

400A AC CLAMP METER

This 400A AC clamp meter combines the features needed for the professional electrician including a built-in non-contact AC Voltage Detector, and Multimeter with Capacitance and Temperature functions.

NON-CONTACT VOLTAGE TESTER
Built-in AC NCV detector

MULTI FUNCTION
11 Functions including:
Capacitance, Frequency, Duty Cycle,
and Temperature functions

EASY TO READ
400 count digital display

COMPACT RUGGED DESIGN
Impact resistant double
molded housing also provides
comfortable grip

11 FUNCTIONS

- AC Current
- AC Voltage
- DC Voltage
- Non-contact AC Voltage
- Resistance
- Capacitance
- Frequency
- Duty Cycle
- Temperature
- Continuity
- Diode Test



Southwire™

TOOLS & EQUIPMENT

[BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.]

1-855-SWT00LS
(855-798-6657)



Southwiretools.com

©2015 Southwire Company, LLC. All rights reserved. Trademark of Southwire Company, LLC.

Features

- Capacitance, Frequency, Duty Cycle and Temperature functions
- Built-in non-contact AC voltage detector
- Impact resistant double molded housing also provides comfortable grip
- CAT III 600V, UL Listed

Includes

- 21010T Clamp meter
- Test leads
- Type K temperature probe with banana plug adapter
- Carrying case
- Two AAA batteries



Specifications

FUNCTION	RANGE	RESOLUTION	ACCURACY ±(% OF READING + DIGITS)
AC CURRENT (50/60Hz)	40.00A	10mA	± (2.8% + 8)
	400.0A	0.1A	
AC VOLTAGE (50 TO 400Hz)	4.000V	1mV	± (1.8% + 8)
	40.00V	10mV	
	400.0V	0.1V	
	600V	1V	± (2.5% + 8)
NCV (NON-CONTACT AC VOLTAGE)	100 to 600V AC		
DC VOLTAGE	400.0mV	0.1mV	± (0.8% + 2)
	4.000V	1mV	± (1.5% + 2)
	40.00V	10mV	
	400.0V	0.1V	
	600V	1V	± (2.0% + 2)
RESISTANCE	400.0Ω	0.1Ω	± (1.0% + 4)
	4.000kΩ	1Ω	
	40.00kΩ	10Ω	
	400.0kΩ	100Ω	± (1.5% + 2)
	4.000MΩ	1kΩ	
	40.00MΩ	10kΩ	
			± (2.5% + 3)
CONTINUITY	Audible beeper if the resistance is <30Ω, beeper off at >150Ω		
DIODE TEST	Typical Test current and Open circuit voltage: 0.3mA/1.5V DC		
CAPACITANCE	40.00nF	10pF	± (4.0% + 20)
	400.0nF	0.1nF	± (3.0% + 5)
	4.000μF	0.001μF	
	40.00μF	0.01μF	
	100.0μF	0.1μF	± (4.0% + 10)
FREQUENCY	10-10kHz	0.01Hz	± (1.5% + 2)
DUTY CYCLE	0.5 to 99.0%	0.1%	± (1.2% + 2)
TEMPERATURE	-4° to 1400°F	0.1°F	± (3.0% + 9°F)
	-20° to 760°F	0.1°C	± (3.0% + 5°C)

GENERAL SPECIFICATIONS

Safety Rating	CAT III 600V
AC Response	Average Responding
Clamp Size	1.2 in. (30mm) approximately
Operation	Autoranging
Auto Power Off	30 min. (approximately)
Display	4000 count LCD
Operating Temperature	41° to 104°F (5° to 40°C)
Storage Temperature	-4° to 140°F (-20° to 60°C)
Batteries	Two AAA
Dimensions	7.9 x 2.6 x 1.5 in. (200 x 66 x 37mm)
Weight	0.45 lbs (205g)

