



# Southwire™

## BEAM ATTACHMENT

# SNAP-CLOSE CONDUIT TO FLANGE CLAMP SIDE AND BOTTOM MOUNT

### APPLICATIONS

Conduit flange mount snap-close clamps support EMT and rigid conduit from beams. Equipped with a rotatable joint, the snap-close conduit clip rotates 360° to position conduit in different directions.

### FEATURES

- Hammer-on installation
- Snap-close conduit clip pivots 360°
- Secures EMT, rigid and aluminum conduit to beams

### MATERIAL/FINISH

Spring Steel/GEOSEAL™

### CERTIFICATIONS

UL Standard: UL 2239



812M58SMTZ



24M58SMTZ



812M24TZ



812M912TZ



Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.

Job Name/Title: \_\_\_\_\_

Model #: \_\_\_\_\_

Contractor: \_\_\_\_\_



# Southwire™

CABLE/CONDUIT

## BEAM ATTACHMENT

# SNAP-CLOSE CONDUIT TO FLANGE CLAMP

PART #	FLANGE THICKNESS	MOUNT OPTION	STATIC LOAD (LBS.)	EMT/RIGID SIZE	FMC SIZE	MC/AC SIZE	BOX QTY.
6M24SMTZ	1/8" – 1/4"	Side	25	---	3/8"	14-2, 12-3	100
16M24SMTZ	1/8" – 1/4"	Side	25	1"	---	---	100
20M24SMTZ	1/8" – 1/4"	Side	25	1-1/4"	---	---	100
24M24SMTZ	1/8" – 1/4"	Side	25	1-1/2"	---	---	50
32M24SMTZ	1/8" – 1/4"	Side	25	2"	---	---	50
812M24SMTZ	1/8" – 1/4"	Side	25	1/2" & 3/4"	---	---	100
16M58SMTZ	5/16" – 1/2"	Side	25	1"	---	---	100
20M58SMTZ	5/16" – 1/2"	Side	25	1-1/4"	---	---	100
24M58SMTZ	5/16" – 1/2"	Side	25	1-1/2"	---	---	50
32M58SMTZ	5/16" – 1/2"	Side	25	2"	---	---	50
812M58SMTZ	5/16" – 1/2"	Side	25	1/2" & 3/4"	---	---	100
6M912SMTZ	9/16" – 3/4"	Side	25	---	3/8"	14-2, 12-3	100
16M912SMTZ	9/16" – 3/4"	Side	25	1"	---	---	100
20M912SMTZ	9/16" – 3/4"	Side	25	1-1/4"	---	---	100
32M912SMTZ	9/16" – 3/4"	Side	25	2"	---	---	50
812M912SMTZ	9/16" – 3/4"	Side	25	1/2" & 3/4"	---	---	100
6M24TZ	1/8" – 1/4"	Bottom	75	---	3/8"	14-2 – 12-3	100
812M24TZ	1/8" – 1/4"	Bottom	75	1/2" & 3/4"	---	---	100
16M24TZ	1/8" – 1/4"	Bottom	75	1"	---	---	100
20M24TZ	1/8" – 1/4"	Bottom	75	1-1/4"	---	---	50
BC18KC112	1/8" – 1/4"	Bottom	75	1-1/2"	---	---	50
32M24TZ	1/8" – 1/4"	Bottom	75	2"	---	---	50
6M58TZ	5/16" – 1/2"	Bottom	75	---	3/8"	14-2 – 12-3	100
812M58TZ	5/16" – 1/2"	Bottom	75	1/2" & 3/4"	---	---	100
BC516KC1	5/16" – 1/2"	Bottom	75	1	---	---	50
BC516KC114	5/16" – 1/2"	Bottom	75	1-1/4"	---	---	50
BC516KC112	5/16" – 1/2"	Bottom	75	1-1/2"	---	---	50
BC516KC2	5/16" – 1/2"	Bottom	75	2"	---	---	50
6M912TZ	9/16" – 3/4"	Bottom	75	---	3/8"	14-2 – 12-3	100
812M912TZ	9/16" – 3/4"	Bottom	75	1/2" & 3/4"	---	---	100
16M912TZ	9/16" – 3/4"	Bottom	75	1"	---	---	50

Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



# Southwire™


## BEAM ATTACHMENTS

# SNAP-CLOSE CONDUIT TO FLANGE CLAMP


PART #	A	B	C	D	E
6M24SMTZ	2.56"	.886"	1.68"	1.26"	.63"
16M24SMTZ	3.41"	.886"	2.52"	1.26"	.63"
20M24SMTZ	3.85"	.886"	2.96"	1.26"	.63"
24M24SMTZ	4.07"	.886"	3.18"	1.26"	.63"
32M24SMTZ	4.77"	.886"	3.88"	1.26"	.63"
812M24SMTZ	2.94"	.886"	2.05"	1.26"	.63"
16M58SMTZ	3.41"	.886"	2.52"	1.26"	.630
20M58SMTZ	3.83"	.886"	2.96"	1.26"	.63"
24M58SMTZ	4.07"	.886"	3.18"	1.26"	.63"
32M58SMTZ	4.77"	.886"	3.88"	1.26"	.63"
812M58SMTZ	2.92"	.886"	2.05"	1.26"	.63"
6M912SMTZ	2.56"	.886"	1.68"	1.26"	.63"
16M912SMTZ	3.39"	.886"	2.52"	1.26"	.63"
20M912SMTZ	3.83"	.886"	2.96"	1.26"	.63"
32M912SMTZ	4.77"	.886"	3.88"	1.26"	.63"
812M912SMTZ	2.92"	.886"	2.05"	1.26"	.63"
6M24TZ	2.74"	1.06"	1.68"	1.50"	.63"
812M24TZ	3.11"	1.06"	2.05"	1.50"	.63"
16M24TZ	3.58"	1.06"	2.52"	1.50"	.63"
20M24TZ	4.02"	1.06"	2.96"	1.50"	.63"
BC18KC112	4.24"	1.06"	3.18"	1.50"	.63"
32M24TZ	5.51"	1.63"	3.88"	1.50"	.63"
6M58TZ	2.97"	1.29"	1.68"	1.50"	.63"
812M58TZ	3.34"	1.29"	2.05"	1.50"	.63"
BC516KC1	3.58"	1.29"	2.52"	1.50"	.63"
BC516KC114	4.02"	1.29"	2.96"	1.50"	.63"
BC516KC112	4.47"	1.29"	3.18"	1.50"	.63"
BC516KC2	5.51"	1.63"	3.88"	1.50"	.63"
6M912TZ	3.31"	1.63"	1.68"	1.75"	.63"
812M912TZ	3.68"	1.63"	2.05"	1.75"	.63"
16M912TZ	4.15"	1.63"	2.52"	1.75"	.63"



24M58SMTZ



812M58TZ



Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.