


Line insulator to Unistrut channel type 3 B including suspension screws KUSYS type 2 with double suspension eye

Item number C2377-01



Dimensions

A: 440 mm
B: 215 mm
C: 90 mm
E: 375 mm
ØD1: 24 mm
ØD2: M12

Material and weight

Material: Kst / INOX / Alu
Weight: 3.8 kg

Loads

Breaking load vertical: 13.5 kN
Tightening torque for bolts and hex-nuts M8: 17 Nm
Tightening torque for suspension screws M12: : 40 Nm

Applicable standards

DIN EN 50119
DIN EN 50124-1
DIN EN 50151
CEI / IEC 60060-1

Function

Insulator body for fastening to Unistrut channel type 3B, in medium to narrow bends. Continuously adjustable double suspension eye allowing the attachment of all type curve rail.

Specifications

Operating voltage: max. 1500 V DC

Comments

Attachment to different types of anchoring rails on request.
The suspension can be mounted to cross-spans or pipes by exchanging the clamp.



Southwire™



A COLAS RAIL COMPANY

Contact Us: Transit@southwire.com