



Southwire™

MOGUL CONDUIT BODIES WITH COVER AND GASKET

C TYPE WITH ROLLERS - HOT DIP GALVANIZED - MALLEABLE IRON

FEATURES

- c(UL)us wet locations
- Built in cable pulling roller
- Threaded NPT tapered hubs for Rigid and IMC conduit
- Smooth and round integral hub bushings protect conductor insulation
- Access to wiring for maintenance and future changes
- Assembled with raised cover, gasket and stainless steel cover screws

APPLICATION

- Provides long and large openings for pulling large conductors, splicing and taps

- Serve as a pull outlets for conductors that are stiff

STANDARD MATERIAL

- Body - Malleable iron
- Gasket - Neoprene rubber
- Screws - Stainless steel

STANDARD FINISH


- Hot dip galvanized

CERTIFICATIONS

- UL Standard: UL 514A - UL 514D
- Fed. Spec: W-C-586D, A-A-50563
- NEMA: FB 1-2014 - NEMA 3R



MC3CGHDG



PART #	SIZE	WIRE SIZE		INTERNAL VOLUME (IN ³)	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	C	D	E	F
		MAX. NUMBER	MAX. SIZE									
MC3CGHDG	1"	3	4 AWG	19	1	4	9.57"	5.98"	---	1.71"	2.19"	1.88"
MC4CGHDG	1-1/4"	3	2 AWG	25	1	6	9.57"	5.98"	---	1.71"	2.19"	2.13"
MC5CGHDG	1-1/2"	3	1/0 AWG	57	1	10	13.75"	10"	9.17"	2.27"	3.03"	2.58"
MC6CGHDG	2"	3	4/0 MCM	75	1	14	13.75"	10"	9.17"	2.27"	3.03"	3.17"
MC7CGHDG	2-1/2"	3	300 MCM	163	1	29	18.40"	15"	10.86"	3.41"	4.27"	3.76"
MC8CGHDG	3"	3	300 MCM	211	1	38	18.40"	15"	10.86"	3.41"	4.27"	4.57"
MC9CGHDG	3-1/2"	3	350 MCM	375	1	56	23.19"	19.98"	15.08"	4.29"	5.31"	5.03"
MC10CGHDG	4"	3	350 MCM	439	1	65	23.19"	19.98"	15.08"	4.29"	5.31"	5.52"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.