



**Southwire™**

# 4" OCTAGON BRACKETED BOXES

1/2" DEEP - DRAWN, FIXTURE EARS 3-1/2" ON CENTER  
FOR CEILING FAN & FIXTURE SUPPORT

### FEATURES

- Mounting hardware included
- 54141-FANWP has tight knockouts and gasket for weatherproof installations

### APPLICATIONS

- Bracketed ceiling fan rated octagon boxes are mounted on the side of a joist or structural member to support ceiling fans or heavy light fixtures

### STANDARD MATERIAL

- Galvanized steel

### CERTIFICATIONS

- UL Listed



54151-FAN



54151-FANWP

PART #	DESCRIPTION	RECOMMENDED MAX LOAD RATINGS		BRACKET TYPE	KNOCKOUTS		CUBIC INCHES (CM <sup>3</sup> )	MASTER QTY.
		CEILING FAN (DYNAMIC) LBS.	FIXTURE (STATIC) LBS.		SIDE CONDUIT	BOTTOM CONDUIT		
54151-FAN	CEILING FAN/LIGHT FIXTURE SUPPORT	70	150	FB	14.0 (229.5)	(3) 1/2"	(3) 1/2", (2) 3/4"	25
54151-FANWP	WEATHERPROOF, CEILING FAN/LIGHT FIXTURE SUPPORT, WITH GROUND WIRE	70	150	FB	14.0 (229.5)	(3) 1/2"	(5) 1/2"	25

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.