

16AWG 2/C STRANDED UNSHIELDED CMP/CL3P/FPLP CABLE

300V, 75C, PLENUM RATED, LOW VOLTAGE POWER LIMITED LV DIMMING

CONSTRUCTION:

1. Conductors: 16 AWG 7/.0192 Stranded Bare Copper 2 Conductors Twisted and Jacketed
2. Insulation: LS-PVC Color : VIOLET, GRAY
3. Shield/Drain: UNSHIELDED
4. Jacket: LS-PVC, Color: WHITE

APPLICATIONS AND FEATURES:

Commercial audio, luminaire, dimming, security and general purpose power limited circuit cable for low voltage cable applications.

SPECIFICATIONS:

- UL 444 CMP, NEC article 800
- Flame Test NFPA 262(UL 910) / CSA FT6
- UL 13 CL3P, NEC article 725
- UL 1424 FPLP, NEC article 760
- CSA C22.2 by C(UL)
- RoHS-2 (European Directive 2011/65/EU)

SAMPLE PRINT LEGEND:

16 AWG 2/C E57497 c{UL}US CMP/CL3P/FPLP 75{D}C -- CMP FT6 MADE IN USA ROHS-3 COMPLIANT -- {MM/DD/YY} {HH:MM} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET

PACKAGING

Standard Length: 1000Ft Reel, other lengths are available upon request.

TABLE 1 - WEIGHTS & MEASUREMENTS

Stock Code	Cond. Size (AWG)	No. of Cond.	No. of Strands	Insulation Thickness (Inch)	Insulation Thickness (mils)	Jacket Thickness (Inch)	Jacket Thickness (mils)	Nominal OD (Inch)	Nominal OD (mils)	Nominal Weight (Lbs/Mft)	Nominal Weight (Kg/Km)
P51641-1	16	2	7/.0192	0.005	0.127	0.014	0.355	0.178	4.521	24.00	35.71

TABLE 2 - ELECTRICALS

Stock Code	Capacitance pF/FT Nom	DC Resistance per Conductor @ 68 DEG. F (Ohms/1M)	Impedance (Ohms)	Velocity of Propagation
P51641-1	43.1	4.35	50	47.5%

Customer Company Name: _____ Date: _____

Customer Approval: _____ Customer Title: _____

All dimensions are nominal and subject to nominal manufacturing tolerances

The customer will accept all factory lengths and +/- 10 percent of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Southwire's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Southwire or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Southwire's standard terms and conditions contained therein, including without limitation Southwire's standard warranty. Southwire disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Southwire. Any information contained herein shall not be disclosed to any party without written consent of Southwire.



Southwire Company, LLC. | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

©2021 Southwire Company, LLC. All Rights Reserved.

