

## Professional VDV Cable Mapper

## QUICKLY TESTS VOICE, DATA AND VIDEO CABLING FOR COMMON WIRING FAULTS.













## Professional VDV Cable Mapper



- EASY-TO-READ LCD DISPLAY WITH BACKLIGHT
- PORT COVERS PROTECT RJ45 AND RJ11 PORTS FROM DUST AND DEBRIS
- BUILT IN TONE GENERATOR FOR CABLE TRACING (SEPARATE AMPLIFIER PROBE REQUIRED)
- MAPS MULTIPLE CABLE RUNS WITH INCLUDED RJ45 & COAX "F" ID REMOTES (5 OF EACH ARE INCLUDED)
- TEST PATCH CABLES OR INSTALLED CABLES







Operating Temperature	32°F to 122°F (0°C to 50°C)
Storage Temperature	-4°F to 140°F (-20°C to 60°C)
Humidity	10% to 90%, non-condensing
Maximum Voltage between any two points	60V DC or 55V AC
without damage	
Batteries	One 9V Battery
Cable Types	Shielded or Unshielded: Cat 7, Cat 7a, Cat 6a,
	Cat 6, Cat 5e, Cat 5, Cat 4, Cat 3, Coax
Maximum Coax Cable Length	1000 feet (305m)
Minimum Cable Length for Split Pair Detection	1.6 feet (0.5m)
Maximum Coax Cable Resistance	100 ohms maximum DC
Dimensions	7.13" X 28.6" X 16.1" (18.1 X 7.3 X 4.1 cm)
Weight	0.78lb (353g)

## INCLUDES

Professional VDV Cable Mapper, ID Remote Kit with 5 RJ45 and 5 Coax Remotes, 9V Battery



BUILT FOR DURABILITY. BUILT FOR RELIABILITY. BUILT FOR WORK."

**1-855-SWTOOLS** (855-798-6657)



Scan code to see more

Southwiretools.com