

## LED Slim Adjustable Wall Pack

### POWER & CCT SELECTABLE



### Lowens the Profile and Raises the Bar

Topaz Slim Adjustable Wall Packs combine customization and control in a slender, hinged housing designed for building exteriors and walkways. The polycarbonate lens adjusts up or down 90 degrees for precise and dark-sky friendly illumination that reduces unnecessary glare and glow. Three wattage and three color temperatures choices offer up to nine different lighting configurations. The integrated dusk-to-dawn photocell automatically turns on or off, conserving energy during the day. Built to withstand harsh outdoor elements, the Slim Adjustable Wall Packs also feature a durable aluminum housing with four NPT 1/2" threaded hubs for additional accessories or conduit.

### FEATURES

- Choose from three wattage and three CCT choices for up to nine possible configurations
- Adjusts up to 90° for precise illumination
- Die cast aluminum housing with IK10 rated impact resistant polycarbonate lens
- Integrated dusk-to-dawn photocell
- Four NPT 1/2" threaded hubs

### SUGGESTED APPLICATIONS

- Commercial and residential
- Security lighting
- Perimeter lighting
- Warehouses
- Condos / apartments
- Hotels



## LED Slim Adjustable Wall Pack POWER & CCT SELECTABLE

### GENERAL SPECIFICATIONS

**Input Voltage, Frequency:** 120-277V, 50/60Hz  
**Power Factor, THD %:** >0.9, <20%  
**Dimming:** 0-10V down to 10%<sup>1</sup>  
**Efficacy:** Up to 140 LPW  
**Minimum CRI:** 84  
**IES Distribution:** Type II

**Functional Life (L70):** 50,000 hours  
**Location Rating:** Wet  
**IP Rating:** IP65  
**IK Rating:** IK10  
**Ambient Operating Temperature:** -40°F to 113°F



**Integrated dusk-to-dawn photocell\***

### ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Lumens	Wattage	Input Current @120V/277V	CCT	DLC Premium ID <sup>+</sup>
WPA-40W-PCTS-BZ-PC	72978	751338039995	3,930	28W	0.26A/0.11A	3000K	PLZDHW0XNLV5
			4,660	35W	0.32A/0.14A	4000K	
			5,270	40W	0.37A/0.16A	5000K	
WPA-75W-PCTS-BZ-PC	72979	751338040007	6,060	45W	0.41A/0.18A	3000K	PLX80URGVHU0
			7,570	60W	0.55A/0.24A	4000K	
			9,440	75W	0.30A/0.69A	5000K	

### NOMENCLATURE

Example: **WPA-40W-PCTS-BZ-PC**


**WPA** = Wall Pack Adjustable - **40W** = 40 Watt - **PCTS** = Power and Color Selectable - **BZ** = Bronze - **PC** = Photocell  
**75W** = 75 Watt

### ENERGY SAVINGS

Catalog Number	LED Wattage	HID Replacement Wattage	Watts Saved	Yearly Savings	5 Year Savings
<b>Based on 12 hours/day and \$0.11/kWh</b>	28W	84W	56W	\$27	\$135
	35W	105W	70W	\$34	\$169
	40W	120W	80W	\$39	\$193
WPA-40W-PCTS-BZ-PC	45W	135W	90W	\$43	\$217
	60W	180W	180W	\$58	\$289
	75W	225W	150W	\$72	\$361

### DIMENSIONS / WEIGHTS

Catalog Number	(A)	(B)	(C)	Weight
WPA-40W-PCTS-BZ-PC	8.50"	11.00"	4.40"	5.2 Lbs.
WPA-75W-PCTS-BZ-PC	8.50"	11.00"	4.40"	5.6 Lbs.



### NOTES:

\*Photocell can easily be disabled (bypassed) by user. Refer to product installation instructions for details.

\*DLC Primary Use: Outdoor Full-Cutoff Wall-Mounted Area Luminaires.

<sup>1</sup>Dimming with standard 0-10V control system or wall dimmers. Dimming complies with IEC60929 Annex E. Fixture may not be compatible with all dimmers. Dimming performance may vary based on selected dimmer. Visit [www.topaz-usa.com/led-dimmer-compatibility](http://www.topaz-usa.com/led-dimmer-compatibility) for up-to-date dimmer compatibility information.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications subject to change without prior notice. Replacement wattage shown depends on application and fixture.

**WARNING:** Some products included in this specification sheet may be subject to the warning requirements of California's Proposition 65. Please refer to your product packaging for more information.