



Southwire™

RIGID WATERTIGHT HUBS

INSULATED THROAT - ALUMINUM

FEATURES

- Raintight, oiltight, and dust tight
- Flame-retardant insulated throat
- Oversized locknut protects against damage from vibration and promotes positive grounding

APPLICATION

- Indoor or outdoor use
- Use to connect Rigid or IMC conduit to a load center or other metal enclosure where a watertight joint is required at knockouts or slip-fit holes

STANDARD MATERIAL

- Aluminum

CERTIFICATIONS


- NEMA 2, 3R, 4, 4X, 5, 12, 13



203



PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B
201AL	1/2"	25	250	22	1.31"	1.54"
202AL	3/4"	10	100	13	1.37"	1.73"
203AL	1"	10	100	18	1.59"	2.04"
204AL	1-1/4"	2	20	5	1.59"	2.42"
205AL	1-1/2"	2	20	7	1.59"	2.79"
206AL	2"	---	10	5	1.59"	3.30"
207AL	2-1/2"	---	5	4	2.44"	3.70"
208AL	3"	---	5	5	2.44"	4.39"
209AL	3-1/2"	---	5	5	2.44"	4.88"
210AL	4"	---	1	2	2.44"	5.50"



Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.