



Southwire™

RIGID WATERTIGHT HUBS

INSULATED THROAT - ZINC DIE CAST

FEATURES

- Raintight, oiltight, and dust tight
- Flame-retardant insulated throat
- Oversized locknut protects against damage from vibrations and promotes positive grounding

APPLICATION

- Indoor or outdoor use
- Use to connect Rigid or IMC conduit to a load center or other metal enclosure where a watertight joint is required at knockouts or slip-fit holes

STANDARD MATERIAL

- Zinc die cast

CERTIFICATIONS


- UL Standard: UL 514B
- Fed. Spec: W-F-406E, W-F-406D
- NEMA: FB 1-2014
- NEMA 2, 3R, 4, 4X, 5, 12, 13



203



PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B
201TZ	1/2"	25	250	49	1.31"	1.54"
202	3/4"	10	100	29	1.37"	1.73"
203	1"	10	100	42	1.59"	2.04"
204	1-1/4"	2	20	12	1.59"	2.42"
205	1-1/2"	2	20	15	1.59"	2.79"
206	2"	2	10	9	1.59"	3.30"
207	2-1/2"	---	5	8	2.44"	3.70"
208	3"	---	5	9	2.44"	4.39"
209	3-1/2"	---	5	11	2.44"	4.88"
210	4"	---	1	3	2.44"	5.50"



Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.