



Southwire™

MECHANICAL LUGS

DOUBLE - DUAL RATED - ALUMINUM

FEATURES

- Two conductor design
- Fast and easy installation
- 90°C temperature rating

APPLICATIONS

- For use with copper or aluminum conductor
- Terminates an electrical conductor to facilitate mechanical connection

STANDARD MATERIAL


- Aluminum
- Steel screw

CERTIFICATIONS

- cULus



2807TZ



PART #	RECOMMENDED TORQUE IN LBS.	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	WIRE RANGE MIN. – MAX.	A	B	C	D
2807TZ	50	10	100	23	#14 – 1/0	1.50"	1.1875"	.8125"	.25"
2808TZ	50	10	100	24	#14 – 2/0	1.50"	1.1875"	.8125"	.25"
2809	275	10	100	26	#6 – 250 MCM	2.5625"	1.625"	1.1875"	.375"
2817TZ	275	4	40	20	#6 – 350 MCM	2.875"	2.9375"	1.25"	.50"
2818	375	6	60	19	#2 – 600 MCM	3.125"	2.375"	1.5625"	.50"
2819	375	6	60	14	300 MCM – 800 MCM	3.50"	2.8125"	1.6875"	.625"

Rev. 0, 10/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.