


LED Emergency Light DOUBLE HEAD



Topaz Puts Safety First

At Topaz, we place a high priority on the safety in the offices, warehouses, retail, and public spaces that you build. Our Emergency Lights are designed to allow easy ceiling or wall mount installations, providing safe and reliable illumination in the event of an emergency. Featuring a high impact, flame retardant thermoplastic housing and adjustable lamp heads that provide 220 lumens of light, the built in 90-minute battery backup will immediately switch on upon failure of the connected power source. This luminaire meets all required NFPA, UL, NEC and OSHA standards.

FEATURES

- Meets NFPA 70, NFPA 101, UL924, NEC/OSHA Standards
- 90-minute battery backup with accessible push to test button
- Dual lamp heads track and swivel for full range of adjustability
- High impact, UL 94-5VA flame retardant housing
- Ceiling or wall mount capable with included hardware

SUGGESTED APPLICATIONS

- Emergency lighting for commercial, industrial, retail and other public spaces
- Stairways, hallways





Job Name/Title: _____ Catalog Number _____

Contractor: _____ Notes: _____

LED Emergency Light DOUBLE HEAD

GENERAL SPECIFICATIONS

Input Voltage, Frequency: 120/277V, 50/60Hz
Input Current: 0.08 / 0.04A
Recharge Time: 24 hours
Emergency Duration/Run Time: 90 minutes
Efficacy: 110 LPW
CRI: 80
Mounting Options: Ceiling or wall mounting capable
Mounting Hardware Included: Wire nuts and screws
Housing: White, high impact, UL 94-5VA flame retardant injection mold thermoplastic with polycarbonate lens
AC Supply Test Button: Yes
Location Rating: Damp
Ambient Operating Temperature: 50°F to 104°F
Battery Type: 3.6V, 1000mAh Ni-Cad



ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Lumens	Input Wattage	Output Wattage	Number of Lamp Heads
EL2/LED/WH	70914	751338037878	220	0.8W	2W	2

Not for sale in California.


NOMENCLATURE

EL2/LED/WH

EL2 = Emergency Light 2 head / LED = LED / WH = White


SPACING GUIDELINES

Mounting Height	Center To Center Spacing	Path of Egress
7.5'	25'	6'
10'	24'	6'



PRODUCT DIMENSIONS / LINE DRAWING

Catalog Number	(A)	(B)	(C)	Weight
EL2/LED/WH	12.5"	4.5"	2.88"	1 Lb.



Compliant NFPA 101 requires 1.0 foot-candle average and 0.1 footcandle minimum with a 40:1 maximum/minimum ratio.

NOTES:

All exit and emergency fixture batteries will be prorated for 5 years.

Specifications subject to change without prior notice.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

WARNING: Some products included in this specification sheet may be subject to the warning requirements of California's Proposition 65. Please refer to your product packaging for more information.

November 2020