



Southwire™

RIGID CONDUIT BODIES

THREADED C TYPE - MALLEABLE IRON

FEATURES

- NPT tapered hubs
- Suitable for use in concrete

APPLICATION

- Provides access to conductors for maintenance and future system changes
- Connects conduit sections

STANDARD MATERIAL

- Malleable iron

STANDARD FINISH


- Zinc plated, aluminum enameled

CERTIFICATIONS

- UL Standard: UL 514A
- Fed. Spec: W-C-586D
- NEMA: FB 1



C1M



PART #	SIZE	WIRE SIZE		INTERNAL VOLUME (IN ³)	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B	C
		MAX. NUMBER	MAX. SIZE						
C1M	1/2"	---	---	4.5	10	7	5.35"	1.31"	1.31"
C2M	3/4"	3	6 AWG	7.5	10	23	6"	1.62"	1.48"
C3M	1"	3	4 AWG	12.5	5	6	7.06"	1.88"	1.75"
C4M	1-1/4"	3	2 AWG	32.3	5	23	9.25"	2.50"	2.40"
C5M	1-1/2"	3	1/0 AWG	35.3	2	26	9.25"	2.67"	2.40"
C6M	2"	3	3/0 AWG	73	1	26	11.50"	3.29"	3.05"
C7M	2-1/2"	3	250 MCM	138	1	10	15"	3.9063"	4.312"
C8M	3"	3	250 MCM	170	1	12	15.125"	4.75"	4.312"
C9M	3-1/2"	3	350 MCM	300	1	21	18.125"	5.1875"	4.875"
C10M	4"	3	350 MCM	328	1	23	18.125"	5.5625"	4.875"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.