



Southwire®

EMT CONNECTORS

COMPRESSION TYPE - STEEL

FEATURES

- Compression type connectors
- Concrete tight
- Assembled with a steel locknut

APPLICATION

- Use to join EMT to box or enclosure

STANDARD MATERIAL

- Steel

STANDARD FINISH

- Zinc plated


CERTIFICATIONS

- UL Standard: UL 514B
- Fed. Spec: W-F-406E, W-F-406D
- NEMA: FB1-2014



652S

| PART # | SIZE | INNER QTY. | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|--------|------------|-------------|---------------------|--------|--------|-------|
| 651S | 1/2" | 25 | 250 | 30 | 1.75" | 1.25" | .406" |
| 652S | 3/4" | 25 | 250 | 43 | 1.813" | 1.563" | .406" |
| 653S | 1" | 10 | 100 | 25 | 2" | 1.813" | .406" |
| 654S | 1-1/4" | --- | 25 | 12 | 2.75" | 2.188" | .50" |
| 655S | 1-1/2" | --- | 20 | 12 | 3" | 2.438" | .50" |
| 656S | 2" | --- | 15 | 15 | 3.188" | 2.938" | .688" |
| 657S | 2-1/2" | --- | 12 | 19 | 3.875" | 3.688" | .75" |
| 658S | 3" | --- | 6 | 15 | 4.375" | 4.313" | .938" |
| 659S | 3-1/2" | --- | 6 | 16 | 4.50" | 4.875" | .938" |
| 660S | 4" | --- | 6 | 21 | 4.75" | 5.375" | .938" |



Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.