



Southwire™

RIGID CONDUIT BODIES

THREADED T TYPE - HOT DIP GALVANIZED

FEATURES

- Hot dip galvanized finish provides superior protection against severe environmental factors

APPLICATION

- Compatible with all Form 5 & Form 35 series conduit bodies and covers
- Provides taps for branch conduit runs
- Enables 90° bends in conduit runs

STANDARD MATERIAL

- Malleable iron

STANDARD FINISH

- Hot dip galvanized

CERTIFICATIONS


- UL Standard: UL 514A and UL514D
- Fed. Spec: A-A-50563
- NEMA: FB 1



T1MHDG



Conforms to finish thickness ASTM A123/123M



PART #	SIZE	WIRE SIZE		INTERNAL VOLUME (IN ³)	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	C
		MAX. NUMBER	MAX. SIZE						
T1MHDG	1/2"	---	---	4	10	9	5.35"	1.31"	2.02"
T2MHDG	3/4"	3	6 AWG	7	10	11	6"	1.62"	2.22"
T3MHDG	1"	3	4 AWG	12	5	8	7.06"	1.88"	2.56"
T4MHDG	1-1/4"	3	2 AWG	33	5	14	7.25"	2.50"	3.50"
T5MHDG	1-1/2"	3	1 AWG	36	2	6	9.25"	2.67"	3.50"
T6MHDG	2"	3	2/0 AWG	76	1	6	11.50"	3.29"	4.25"
T7MHDG	2-1/2"	3	300 MCM	146	1	12	15"	3.94"	5.72"
T8MHDG	3"	3	300 MCM	185	1	15	15.125"	4.75"	8.88"
T9MHDG	3-1/2"	3	350 MCM	300	1	27	18.125"	5.20"	6.81"
T10MHDG	4"	3	350 MCM	330	1	28	18.125"	5.56"	7.20"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.