



QWIKrope®

An innovative new high performance pulling rope that is UV resistant, lightweight and ultra low stretch for all your feeder and circuit wire solutions.

Features & Benefits:

- High performance pulling rope made from ultra high molecular weight polyethylene fibers
- 12 Strand single braided 9/16" pulling rope with a breaking strength of 32,000 lbs., pound for pound stronger than steel
- 2 sizes for all your circuit wire pulls: 1/8" pulling rope with a breaking strength of 1,100 lbs., and a 1/4" pulling rope with a breaking strength of 7,500 lbs.
- Ultra low stretch, UV resistant, lightweight pulling rope
- 24% reduction in the coefficient of friction, as compared to traditional pulling ropes
- Dual factory installed pulling eyes
- Does not absorb water, no rope rot
- Need only one size rope (9/16") for feeder conductor pulls up to 10,000 lbs.
- 1/8" QWIKrope® can easily be vacuumed into any conduit run up to 290 ft.
- 9/16" QWIKrope® recommended for use with M3K, M6K, and XD10 cable pullers



HI-TECH CONSTRUCTION

SUPERIOR STRENGTH

HIGHLY DURABLE

READY TO USE



QWIKrope® for use in feeder conductor pulls

MODEL #	STOCK#	DIA. (IN)	CIRC. (IN)	LENGTH	AVG BREAKING STRENGTH (LBS)	TOTAL WEIGHT
SPR9612	58305901	9/16"	1 3/4"	1,200 ft.	32,000 lbs.	103 lbs.
SPR969	58305801	9/16"	1 3/4"	900 ft.	32,000 lbs.	77 lbs.
SPR966	58305701	9/16"	1 3/4"	600 ft.	32,000 lbs.	52 lbs.
SPR963	58305601	9/16"	1 3/4"	300 ft.	32,000 lbs.	26 lbs.

QWIKrope® for use in circuit wire pulls

MODEL #	STOCK#	DIA. (IN)	CIRC. (IN)	LENGTH	AVG BREAKING STRENGTH (LBS)	TOTAL WEIGHT
SPR183	58387401	1/8"	3/8"	300 ft.	1,100 lbs.	2.5 lbs.
SPR186	64865701	1/8"	3/8"	600 ft.	1,100 lbs.	5 lbs.
SPR143	58387501	1/4"	3/4"	300 ft.	7,500 lbs.	6.5 lbs.
SPR146	58526301	1/4"	3/4"	600 ft.	7,500 lbs.	11 lbs.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**