

Report of Test

LLIA002581-008

Indoor Distribution Photometry Test Report

Catalog Number: RDL4-ADJ-7W-CS 4000K Setting
Recessed mounted, formed white painted aluminum housing,
white interior reflector, diffuse white plastic enclosure.
18 white LEDs, switch set for 4000K.
One Topaz RDL4-ADJ-7W-CS LED driver in formed steel box.




Prepared For:
Topaz Lighting, A Southwire Company
925 Waverly Avenue
Holtsville, NY 11742, USA

Performance Summary			
Input Voltage	120.0 Vac	Luminous Flux	609.6 Lumens
Input Current	0.0559 A	Total Efficacy	96.0 Lm/W
Input Power	6.35 W	Downward Flux	609.6 Lumens
Frequency	60.00 Hz	Downward Flux	100.0 % of Total
Power Factor	0.947		
Current THD	19.3 %		


This test report was issued by LightLab International Allentown, LLC without alterations or erasures.

Test date: 01/29/2025
Report date: 02/05/2025


Signed: _____



Report of Test
LLIA002581-008



Zonal Flux Summary										
Zone (Deg Vert)	Flux (Lumens)	Percent of Total		Zone (Deg Vert)	Flux (Lumens)	Percent of Total		Zone (Deg Vert)	Flux (Lumens)	Percent of Total
0-10	23.0	3.8%		90-100	0.0	0.0%		0-20	87.7	14.4%
10-20	64.7	10.6%		100-110	0.0	0.0%		0-30	182.6	29.9%
20-30	94.9	15.6%		110-120	0.0	0.0%		0-40	292.0	47.9%
30-40	109.5	18.0%		120-130	0.0	0.0%		0-60	493.9	81.0%
40-50	108.3	17.8%		130-140	0.0	0.0%		0-80	600.0	98.4%
50-60	93.6	15.4%		140-150	0.0	0.0%		10-90	586.6	96.2%
60-70	68.4	11.2%		150-160	0.0	0.0%		20-50	312.6	51.3%
70-80	37.6	6.2%		160-170	0.0	0.0%		40-90	317.5	52.1%
80-90	9.6	1.6%		170-180	0.0	0.0%		60-90	115.6	19.0%
0-90	609.6	100.0%		90-180	0.0	0.0%		0-180	609.6	100.0%



Report of Test

LLIA002581-008

Luminous Intensity (Candela) Table

		Lateral (C-Plane) Angles								
		0	22.5	45	67.5	90	112.5	135	157.5	180
Vertical (Gamma) Angles - Data was acquired in 0.5° increments, 2.5° increments shown.	0	244	244	244	244	244	244	244	244	244
	2.5	244	244	244	244	244	244	244	244	244
	5	242	242	242	242	242	242	242	242	242
	7.5	240	240	240	240	240	240	240	240	240
	10	238	238	238	238	238	238	238	238	238
	12.5	234	234	234	234	234	234	234	234	234
	15	230	230	230	230	230	230	230	230	230
	17.5	225	225	225	225	225	225	225	225	225
	20	219	219	219	219	219	219	219	219	219
	22.5	213	213	213	213	213	213	213	213	213
	25	206	206	206	206	206	206	206	206	206
	27.5	199	199	199	199	199	199	199	199	199
	30	191	191	191	191	191	191	191	191	191
	32.5	183	183	183	183	183	183	183	183	183
	35	175	175	175	175	175	175	175	175	175
	37.5	167	167	167	167	167	167	167	167	167
	40	158	158	158	158	158	158	158	158	158
	42.5	149	149	149	149	149	149	149	149	149
	45	140	140	140	140	140	140	140	140	140
	47.5	132	132	132	132	132	132	132	132	132
50	123	123	123	123	123	123	123	123	123	
52.5	114	114	114	114	114	114	114	114	114	
55	105	105	105	105	105	105	105	105	105	
57.5	96	96	96	96	96	96	96	96	96	
60	87	87	87	87	87	87	87	87	87	
62.5	78	78	78	78	78	78	78	78	78	
65	69	69	69	69	69	69	69	69	69	
67.5	60	60	60	60	60	60	60	60	60	
70	52	52	52	52	52	52	52	52	52	
72.5	44	44	44	44	44	44	44	44	44	
75	35	35	35	35	35	35	35	35	35	
77.5	28	28	28	28	28	28	28	28	28	
80	21	21	21	21	21	21	21	21	21	
82.5	14	14	14	14	14	14	14	14	14	
85	8	8	8	8	8	8	8	8	8	
87.5	3	3	3	3	3	3	3	3	3	
90	0	0	0	0	0	0	0	0	0	

16 lateral half-planes of data were acquired, 22.5 degree increments shown.

North America (issuing laboratory)


LightLab International Allentown, LLC
905 Harrison Street, Suite 135
Allentown, PA 18103 USA

Ph: +1 484-273-0705
Fx: +1 484-209-5779
www.lightlaballentown.com

Australasia & S.E. Asia

LightLab International
50 Redcliffe Gardens Drive
Clontarf - Queensland, 4019, Australia

Ph : +61 7 3283 7862
Fx : +61 7 3283 8751
www.lightlabint.com



Report of Test

LLIA002581-008

Luminous Intensity (Candela) Table

		Lateral (C-Plane) Angles								
		0	22.5	45	67.5	90	112.5	135	157.5	180
Vertical (Gamma) Angles - Data was acquired in 0.5° increments, 2.5° increments shown.	90	0	0	0	0	0	0	0	0	0
	92.5	0	0	0	0	0	0	0	0	0
	95	0	0	0	0	0	0	0	0	0
	97.5	0	0	0	0	0	0	0	0	0
	100	0	0	0	0	0	0	0	0	0
	102.5	0	0	0	0	0	0	0	0	0
	105	0	0	0	0	0	0	0	0	0
	107.5	0	0	0	0	0	0	0	0	0
	110	0	0	0	0	0	0	0	0	0
	112.5	0	0	0	0	0	0	0	0	0
	115	0	0	0	0	0	0	0	0	0
	117.5	0	0	0	0	0	0	0	0	0
	120	0	0	0	0	0	0	0	0	0
	122.5	0	0	0	0	0	0	0	0	0
	125	0	0	0	0	0	0	0	0	0
	127.5	0	0	0	0	0	0	0	0	0
	130	0	0	0	0	0	0	0	0	0
	132.5	0	0	0	0	0	0	0	0	0
	135	0	0	0	0	0	0	0	0	0
	137.5	0	0	0	0	0	0	0	0	0
	140	0	0	0	0	0	0	0	0	0
	142.5	0	0	0	0	0	0	0	0	0
	145	0	0	0	0	0	0	0	0	0
	147.5	0	0	0	0	0	0	0	0	0
	150	0	0	0	0	0	0	0	0	0
	152.5	0	0	0	0	0	0	0	0	0
	155	0	0	0	0	0	0	0	0	0
	157.5	0	0	0	0	0	0	0	0	0
	160	0	0	0	0	0	0	0	0	0
	162.5	0	0	0	0	0	0	0	0	0
165	0	0	0	0	0	0	0	0	0	
167.5	0	0	0	0	0	0	0	0	0	
170	0	0	0	0	0	0	0	0	0	
172.5	0	0	0	0	0	0	0	0	0	
175	0	0	0	0	0	0	0	0	0	
177.5	0	0	0	0	0	0	0	0	0	
180	0	0	0	0	0	0	0	0	0	

16 lateral half-planes of data were acquired, 22.5 degree increments shown.



Report of Test

LLIA002581-008

Coefficients of Utilization/Room Utilization - Zonal Cavity Method																					
Effective Floor Cavity Reflectance 0.20																					
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100
1	109	105	100	97	106	102	99	95	98	95	92	89	94	92	89	86	91	89	87	85	85
2	100	92	85	79	97	90	84	78	86	81	77	73	83	79	75	71	80	76	73	71	71
3	91	81	73	66	89	79	72	66	76	70	65	61	73	68	64	60	71	66	62	60	60
4	84	72	63	57	81	70	62	56	68	61	55	50	66	60	55	51	64	58	54	52	52
5	77	64	56	49	75	63	55	49	61	54	48	43	59	53	48	44	57	52	47	45	45
6	71	58	49	43	69	57	49	43	55	48	42	37	54	47	42	38	52	46	42	40	40
7	66	53	44	38	64	52	44	38	50	43	38	33	49	42	37	33	48	42	37	35	35
8	62	48	40	34	60	48	40	34	46	39	34	29	45	38	34	30	44	38	33	32	32
9	58	44	36	31	56	44	36	31	43	36	31	26	42	35	30	26	41	35	30	28	28
10	54	41	33	28	53	41	33	28	40	33	28	23	39	32	28	23	38	32	28	26	26


For absolute test reports, RUs are expressed as a percentage of total lumen output. For relative test reports, CUs are expressed as a percentage of total lamp output. Calculations were based on published IES procedures, and are based on the zonal cavity method. Basic assumptions: 1) Room surfaces are lambertian reflectors. 2) Incident flux on each surface is uniformly distributed. 3) The room is spectrally neutral. When luminaires are not evenly distributed throughout the room, or do not exhibit lateral symmetry, CU values may differ from actual performance.

Circle of Light Plot			
Height(ft)	Illuminance at Nadir (fc)	Ground-level distance to half-of-nadir illuminance (ft)	
		0-180 deg	90-270 deg
6.0	6.8	7.04	7.04
8.0	3.8	9.38	9.38
10.0	2.4	11.73	11.73
12.0	1.7	14.07	14.07
14.0	1.2	16.42	16.42
16.0	1.0	18.76	18.76

Spacing Criterion	
SC:	1.2

Average Luminance (cd/m ²)			
	0 deg Plane	45 deg Plane	90 deg Plane
0	53514	53514	53514
45	43536	43536	43536
55	40019	40019	40019
65	35861	35861	35861
75	30003	30003	30003
85	20529	20529	20529

Beam and Field Angle	
0-180 Degree Plane	
Beam Angle:	100.3°
Field Angle:	157.3°
90-270 Degree Plane	
Beam Angle:	100.3°
Field Angle:	157.3°



Report of Test

LLIA002581-008

UGR Table - Corrected

Reflectances

Ceiling Cavity	70	70	50	50	30	70	70	50	50	30
Walls	50	30	50	30	30	50	30	50	30	30
Floor Cavity	20	20	20	20	20	20	20	20	20	20


Room Size

UGR Viewed Crosswise

UGR Viewed Endwise


X=2H	Y=2H	23.9	25.5	24.3	25.9	26.2	23.9	25.5	24.3	25.9	26.2
	3H	25.6	27.1	26.0	27.4	27.8	25.6	27.1	26.0	27.4	27.8
	4H	26.2	27.6	26.6	27.9	28.3	26.2	27.6	26.6	27.9	28.3
	6H	26.7	27.9	27.1	28.3	28.7	26.7	27.9	27.1	28.3	28.7
	8H	26.8	28.0	27.2	28.4	28.8	26.8	28.0	27.2	28.4	28.8
	12H	26.9	28.0	27.3	28.4	28.8	26.9	28.0	27.3	28.4	28.8
4H	2H	24.5	25.9	24.9	26.2	26.6	24.5	25.9	24.9	26.2	26.6
	3H	26.5	27.6	26.9	28.0	28.4	26.5	27.6	26.9	28.0	28.4
	4H	27.2	28.2	27.6	28.6	29.0	27.2	28.2	27.6	28.6	29.0
	6H	27.7	28.6	28.2	29.0	29.5	27.7	28.6	28.2	29.0	29.5
	8H	27.9	28.7	28.3	29.2	29.6	27.9	28.7	28.3	29.2	29.6
	12H	28.0	28.7	28.5	29.2	29.7	28.0	28.7	28.5	29.2	29.7
8H	4H	27.5	28.3	27.9	28.7	29.2	27.5	28.3	27.9	28.7	29.2
	6H	28.1	28.8	28.6	29.3	29.8	28.1	28.8	28.6	29.3	29.8
	8H	28.3	29.0	28.8	29.5	29.9	28.3	29.0	28.8	29.5	29.9
	12H	28.5	29.1	29.0	29.5	30.1	28.5	29.1	29.0	29.5	30.1
12H	4H	27.5	28.2	28.0	28.7	29.2	27.5	28.2	28.0	28.7	29.2
	6H	28.2	28.8	28.7	29.2	29.8	28.2	28.8	28.7	29.2	29.8
	8H	28.4	29.0	28.9	29.5	30.0	28.4	29.0	28.9	29.5	30.0

Maximum UGR = 30.1




Report of Test LLIA002581-008

Iso-Illuminance Plot



The isofootcandle values shown in the plot above are based on a mounting height of $h = 8.0$ feet. Grid values show multiples of mounting height. The isoilluminance contour lines are expressed in units of footcandles. The values expressed are based on the direct light from a single unit without the contribution of room reflections.



Report of Test

LLIA002581-008

Test Distance 9.5 m
Ambient Temperature 25.0 °C

Notes

The laboratory has not participated in the selection of samples to be tested. All testing is performed on the understanding that the significance of the report is limited to the extent that the test sample is representative of production units.

Tested in accordance with the applicable sections of IES LM-79-19. Format of reports and angular increments based on IES LM-41-20 and LM-46-20.

The luminous intensity values, and other derived quantities, contained in this report are based on the absolute data, as measured.

Prorating the performance of the sample for the use of other component combinations (such as lamp / LED / Ballast / driver), or for use in different environmental conditions than that tested, may produce erroneous results.

This report is free of erasures and corrections.

Photometric intensity values are reported using the CIE C-Gamma coordinate system as defined in CIE publication number 121.

This report may contain data that are not covered by the NVLAP accreditation. Quantities marked with ‡ are not covered.

This report must not be used by the customer to claim product certification, approval or endorsement by NVLAP, NIST, or any agency of the Federal Government.