



# Southwire™

## RIGID CONDUIT BODIES

### THREADED C TYPE - HOT DIP GALVANIZED

#### FEATURES

- Hot dip galvanized finish provides superior protection against severe environmental factors

#### APPLICATION

- Compatible with all Form 5 & Form 35 series conduit bodies and covers
- Provides taps for branch conduit runs
- Enables 90° bends in conduit runs

#### STANDARD MATERIAL

- Malleable iron

#### STANDARD FINISH

- Hot dip galvanized

#### CERTIFICATIONS


- UL Standard: UL 514A and UL514D
- Fed. Spec: A-A-50563
- NEMA: FB 1



C1MHDG



Conforms to finish thickness ASTM A123/123M



PART #	SIZE	WIRE SIZE		INTERNAL VOLUME (IN <sup>3</sup> )	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B	C
		MAX. NUMBER	MAX. SIZE						
C1MHDG	1/2"	---	---	4.5	10	6	5.43"	1.46"	1.36"
C2MHDG	3/4"	3	6 AWG	7.5	10	9	6.18"	1.65"	1.57"
C3MHDG	1"	3	4 AWG	12.5	5	6	7.16"	1.98"	1.79"
C4MHDG	1-1/4"	3	2 AWG	32.3	5	12	9"	2.60"	2.52"
C5MHDG	1-1/2"	3	1/0 AWG	35.3	2	6	9.07"	2.80"	2.52"
C6MHDG	2"	3	3/0 AWG	73	1	6	11.54"	3.52"	3.15"
C7MHDG	2-1/2"	3	250 MCM	138	1	10	15.28"	3.98"	4.45"
C8MHDG	3"	3	250 MCM	170	1	15	15.39"	4.65"	4.45"
C9MHDG	3-1/2"	3	350 MCM	300	1	27	18.30"	5.43"	5.53"
C10MHDG	4"	3	350 MCM	328	1	24	18.30"	5.74"	5.53"

Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.