



Southwire™

RIGID OFFSET NIPPLES

3/4" OFFSET - HOT DIP GALVANIZED - MALLEABLE IRON

FEATURES

- NPSM thread: Smooth inside surface to facilitate wire pulling free of damage

APPLICATION

- Indoor or outdoor use
- Use as an offset connector between two enclosures
- Offsets the axis of the raceways by 3/4"

STANDARD MATERIAL

- Malleable iron

STANDARD FINISH

- Hot dip galvanized

CERTIFICATIONS

- UL Standard: UL 514B
- RoHS
- Fed. Spec: A-A-50553
- NEMA: FB 1




11MHDG



Conforms to finish thickness
ASTM A123/123M

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B	C
111MHDG	1/2"	10	100	20	2.81"	1.02"	.75"
112MHDG	3/4"	10	100	29	2.75"	1.25"	.75"
113MHDG	1"	5	50	39	2.87"	1.56"	.75"
114MHDG	1-1/4"	5	50	32	3.13"	2"	.75"
115MHDG	1-1/2"	4	40	40	3.13"	2.31"	.75"
116MHDG	2"	2	20	21	3.06"	2.76"	.75"
117MHDG	2-1/2"	---	2	3	3.97"	3.26"	.75"
118MHDG	3"	---	2	5	4.43"	3.81"	.75"
119MHDG	3-1/2"	---	1	4	4.82"	4.38"	.75"
119AMHDG	4"	---	1	4	5.04"	4.96"	.75"



Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.