




Southwire®

MCF01

MAXIS® FEEDER

A revolutionary new way to feed wire quickly and efficiently.



VERSATILE

Handles wire sizes from 3/0 - 3 1/2" cable

FAST AND EFFICIENT

Quick 1 person setup and operate

SUPERIOR GRIP

Grooved serpentine roller design for increased traction force

INCREASED PULLING FORCE

1,600 lb capacity on 4 – SIMpull® THHN 500 MCM conductors

ADJUSTABLE

Easily adjust wire tension, even during operation

HEAVY DUTY RUBBER WHEELS

Easy jobsite maneuverability and will never go flat



Southwire™

TOOLS & EQUIPMENT

[BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.]

**1-855-SWTOOLS
(855-798-6657)**



Southwiretools.com

Features & Benefits

- Designed and built specifically to accommodate Southwire[®] SIMpull[®] wire
- Quick 1 person set-up and operate
- Forward and reverse, variable speed, feeds up to 30 fpm.
- May be used with the Triggers[®] remote foot switches for simultaneous feeder/puller control
- Easily adjust wire tension, even during operation
- Fast 2 minute setup, wire sizes from 3/0 - 3 1/2" cable
- Solid rubber tires and swivel casters for easy jobsite maneuverability and will never go flat
- Digital footage meter allows easy monitoring of approx. conductor length being fed
- Uses grooved serpentine roller design with increased surface area for increased traction force (no pneumatic tires)
- Dual anchoring mechanism
- Maximum traction force: single conductor 800 lbs, 4 Conductors 1,600 lb capacity on SIMpull[®] THHN 500 MCM
- Cable capacity: 8 x 250 MCM, 6 x 500 MCM, 5 x 750 MCM



Specifications

MODEL #	STOCK#	DESCRIPTION	LENGTH	WIDTH	HEIGHT	WEIGHT
MCF01	58133301	Cable Feeder	35"	26"	44"	366 lbs

