




Report of Test

LLIA002581-006

Indoor Distribution Photometry Test Report

Catalog Number: RDL6-SQ-9W-CS 4000K Setting
Recessed mounted, formed white painted aluminum housing,
white interior reflector, diffuse white plastic enclosure.
60 white LEDs, switch set for 4000K.
One Topaz RDL6-SQ-9W-CS LED driver in formed steel box.



Prepared For:
Topaz Lighting, A Southwire Company
925 Waverly Avenue
Holtsville, NY 11742, USA

Performance Summary			
Input Voltage	120.0 Vac	Luminous Flux	853.1 Lumens
Input Current	0.0767 A	Total Efficacy	96.0 Lm/W
Input Power	8.89 W	Downward Flux	853.1 Lumens
Frequency	60.00 Hz	Downward Flux	100.0 % of Total
Power Factor	0.966		
Current THD	14.6 %		


This test report was issued by LightLab International Allentown, LLC without alterations or erasures.

Test date: 01/28/2025
Report date: 02/03/2025

Signed: _____



Report of Test
LLIA002581-006



Zonal Flux Summary										
Zone (Deg Vert)	Flux (Lumens)	Percent of Total		Zone (Deg Vert)	Flux (Lumens)	Percent of Total		Zone (Deg Vert)	Flux (Lumens)	Percent of Total
0-10	30.2	3.5%		90-100	0.0	0.0%		0-20	115.8	13.6%
10-20	85.6	10.0%		100-110	0.0	0.0%		0-30	243.0	28.5%
20-30	127.3	14.9%		110-120	0.0	0.0%		0-40	392.5	46.0%
30-40	149.5	17.5%		120-130	0.0	0.0%		0-60	675.5	79.2%
40-50	150.5	17.6%		130-140	0.0	0.0%		0-80	836.3	98.0%
50-60	132.5	15.5%		140-150	0.0	0.0%		10-90	822.9	96.5%
60-70	100.6	11.8%		150-160	0.0	0.0%		20-50	427.2	50.1%
70-80	60.2	7.1%		160-170	0.0	0.0%		40-90	460.6	54.0%
80-90	16.8	2.0%		170-180	0.0	0.0%		60-90	177.6	20.8%
0-90	853.1	100.0%		90-180	0.0	0.0%		0-180	853.1	100.0%



Report of Test

LLIA002581-006

Luminous Intensity (Candela) Table

		Lateral (C-Plane) Angles								
		0	22.5	45	67.5	90	112.5	135	157.5	180
Vertical (Gamma) Angles - Data was acquired in 0.5° increments, 2.5° increments shown.	0	320	320	320	320	320	320	320	320	320
	2.5	319	319	319	319	320	319	319	319	319
	5	318	318	318	318	318	318	318	318	318
	7.5	316	316	316	316	316	316	316	316	316
	10	313	312	312	312	313	312	312	312	313
	12.5	308	308	308	308	309	308	308	308	308
	15	304	304	304	304	304	304	304	304	304
	17.5	298	298	298	298	298	298	298	298	298
	20	291	291	291	291	292	291	291	291	291
	22.5	284	284	284	284	284	284	284	284	284
	25	276	276	276	276	277	276	276	276	276
	27.5	268	268	268	268	268	268	268	268	268
	30	259	259	259	259	259	259	259	259	259
	32.5	249	249	249	249	249	249	249	249	249
	35	239	239	239	239	239	239	239	239	239
	37.5	229	228	228	229	229	229	228	228	229
	40	218	217	218	218	218	218	218	217	218
	42.5	206	206	206	207	207	207	206	206	206
	45	195	195	195	195	196	195	195	195	195
	47.5	183	183	183	184	184	184	183	183	183
50	172	172	172	172	172	172	172	172	172	
52.5	160	160	160	160	160	160	160	160	160	
55	148	148	148	148	149	148	148	148	148	
57.5	136	136	136	137	137	137	136	136	136	
60	125	124	125	125	125	125	125	124	125	
62.5	113	113	113	113	113	113	113	113	113	
65	102	101	101	102	102	102	101	101	102	
67.5	90	90	90	90	91	90	90	90	90	
70	79	79	79	79	79	79	79	79	79	
72.5	68	68	68	68	68	68	68	68	68	
75	57	57	57	57	57	57	57	57	57	
77.5	46	46	46	46	46	46	46	46	46	
80	35	35	35	36	36	36	35	35	35	
82.5	25	25	25	25	25	25	25	25	25	
85	15	15	15	15	15	15	15	15	15	
87.5	6	5	5	5	6	5	5	5	6	
90	0	0	0	0	0	0	0	0	0	

16 lateral half-planes of data were acquired, 22.5 degree increments shown.



Report of Test

LLIA002581-006

Luminous Intensity (Candela) Table

		Lateral (C-Plane) Angles									
		0	22.5	45	67.5	90	112.5	135	157.5	180	
Vertical (Gamma) Angles - Data was acquired in 0.5° increments, 2.5° increments shown.	90	0	0	0	0	0	0	0	0	0	
	92.5	0	0	0	0	0	0	0	0	0	
	95	0	0	0	0	0	0	0	0	0	
	97.5	0	0	0	0	0	0	0	0	0	
	100	0	0	0	0	0	0	0	0	0	
	102.5	0	0	0	0	0	0	0	0	0	
	105	0	0	0	0	0	0	0	0	0	
	107.5	0	0	0	0	0	0	0	0	0	
	110	0	0	0	0	0	0	0	0	0	
	112.5	0	0	0	0	0	0	0	0	0	
	115	0	0	0	0	0	0	0	0	0	
	117.5	0	0	0	0	0	0	0	0	0	
	120	0	0	0	0	0	0	0	0	0	
	122.5	0	0	0	0	0	0	0	0	0	
	125	0	0	0	0	0	0	0	0	0	
	127.5	0	0	0	0	0	0	0	0	0	
	130	0	0	0	0	0	0	0	0	0	
	132.5	0	0	0	0	0	0	0	0	0	
	135	0	0	0	0	0	0	0	0	0	
	137.5	0	0	0	0	0	0	0	0	0	
140	0	0	0	0	0	0	0	0	0		
142.5	0	0	0	0	0	0	0	0	0		
145	0	0	0	0	0	0	0	0	0		
147.5	0	0	0	0	0	0	0	0	0		
150	0	0	0	0	0	0	0	0	0		
152.5	0	0	0	0	0	0	0	0	0		
155	0	0	0	0	0	0	0	0	0		
157.5	0	0	0	0	0	0	0	0	0		
160	0	0	0	0	0	0	0	0	0		
162.5	0	0	0	0	0	0	0	0	0		
165	0	0	0	0	0	0	0	0	0		
167.5	0	0	0	0	0	0	0	0	0		
170	0	0	0	0	0	0	0	0	0		
172.5	0	0	0	0	0	0	0	0	0		
175	0	0	0	0	0	0	0	0	0		
177.5	0	0	0	0	0	0	0	0	0		
180	0	0	0	0	0	0	0	0	0		

16 lateral half-planes of data were acquired, 22.5 degree increments shown.



Report of Test

LLIA002581-006

Coefficients of Utilization/Room Utilization - Zonal Cavity Method																					
Effective Floor Cavity Reflectance 0.20																					
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	104	100	96	106	102	98	94	97	94	91	94	91	88	90	88	86	84			
2	99	91	84	78	96	89	83	77	85	80	75	82	78	74	79	75	72	70			
3	90	80	72	65	88	78	71	65	75	69	63	72	67	62	70	65	61	59			
4	83	71	62	55	80	69	61	55	67	60	54	65	58	53	62	57	53	50			
5	76	63	54	48	74	62	54	47	60	53	47	58	52	46	56	50	46	44			
6	70	57	48	42	68	56	48	42	54	47	41	53	46	41	51	45	40	38			
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	47	41	36	34			
8	61	47	39	33	59	47	39	33	45	38	33	44	37	33	43	37	32	30			
9	57	43	35	30	55	43	35	30	42	35	30	41	34	29	40	34	29	27			
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25			

For absolute test reports, RUs are expressed as a percentage of total lumen output. For relative test reports, CUs are expressed as a percentage of total lamp output. Calculations were based on published IES procedures, and are based on the zonal cavity method. Basic assumptions: 1) Room surfaces are lambertian reflectors. 2) Incident flux on each surface is uniformly distributed. 3) The room is spectrally neutral. When luminaires are not evenly distributed throughout the room, or do not exhibit lateral symmetry, CU values may differ from actual performance.

Circle of Light Plot			
Height(ft)	Illuminance at Nadir (fc)	Ground-level distance to half-of-nadir illuminance (ft)	
		0-180 deg	90-270 deg
6.0	8.9	7.23	7.24
8.0	5.0	9.64	9.65
10.0	3.2	12.06	12.07
12.0	2.2	14.47	14.48
14.0	1.6	16.88	16.89
16.0	1.2	19.29	19.30

Spacing Criterion	
0 deg:	1.2
90 deg:	1.2
180 deg:	1.2
270 deg:	1.2

Average Luminance (cd/m ²)			
	0 deg Plane	45 deg Plane	90 deg Plane
0	33018	33018	33018
45	28484	28461	28541
55	26643	26640	26743
65	24796	24767	24908
75	22697	22741	22841
85	17797	17258	18112

Beam and Field Angle	
0-180 Degree Plane	
Beam Angle:	105.0°
Field Angle:	161.6°
90-270 Degree Plane	
Beam Angle:	105.2°
Field Angle:	161.8°



Report of Test

LLIA002581-006

UGR Table - Corrected

Reflectances

Ceiling Cavity	70	70	50	50	30	70	70	50	50	30
Walls	50	30	50	30	30	50	30	50	30	30
Floor Cavity	20	20	20	20	20	20	20	20	20	20

Room Size

UGR Viewed Crosswise

UGR Viewed Endwise


X=2H	Y=2H	23.4	25.1	23.8	25.4	25.7	23.5	25.1	23.8	25.4	25.7
		25.3	26.8	25.7	27.1	27.5	25.3	26.8	25.7	27.1	27.5
	3H	26.0	27.4	26.4	27.8	28.1	26.0	27.4	26.4	27.8	28.2
	4H	26.6	27.9	27.0	28.2	28.6	26.6	27.9	27.0	28.3	28.6
	6H	26.8	28.0	27.2	28.4	28.8	26.8	28.0	27.2	28.4	28.8
	12H	26.9	28.1	27.3	28.4	28.9	26.9	28.1	27.4	28.5	28.9
4H	2H	24.1	25.5	24.5	25.8	26.2	24.1	25.5	24.5	25.8	26.2
	3H	26.2	27.3	26.6	27.7	28.1	26.2	27.4	26.6	27.8	28.2
	4H	27.0	28.1	27.5	28.5	28.9	27.0	28.1	27.5	28.5	29.0
	6H	27.7	28.6	28.2	29.1	29.5	27.7	28.7	28.2	29.1	29.6
	8H	27.9	28.8	28.4	29.3	29.7	28.0	28.8	28.4	29.3	29.8
	12H	28.1	28.9	28.6	29.4	29.8	28.2	28.9	28.6	29.4	29.9
8H	4H	27.4	28.2	27.8	28.7	29.1	27.4	28.2	27.8	28.7	29.2
	6H	28.2	28.9	28.7	29.4	29.9	28.2	28.9	28.7	29.4	29.9
	8H	28.5	29.1	29.0	29.7	30.1	28.5	29.2	29.0	29.7	30.2
	12H	28.7	29.3	29.2	29.8	30.4	28.8	29.3	29.3	29.8	30.4
12H	4H	27.4	28.2	27.9	28.7	29.1	27.4	28.2	27.9	28.7	29.1
	6H	28.3	28.9	28.8	29.4	29.9	28.3	28.9	28.8	29.4	29.9
	8H	28.6	29.2	29.1	29.7	30.2	28.6	29.2	29.2	29.7	30.3

Maximum UGR = 30.4



Report of Test
LLIA002581-006

Iso-Illuminance Plot



The isofootcandle values shown in the plot above are based on a mounting height of $h = 8.0$ feet. Grid values show multiples of mounting height. The isoilluminance contour lines are expressed in units of footcandles. The values expressed are based on the direct light from a single unit without the contribution of room reflections.



Report of Test

LLIA002581-006

Test Distance 9.5 m
Ambient Temperature 25.1 °C

Notes

The laboratory has not participated in the selection of samples to be tested. All testing is performed on the understanding that the significance of the report is limited to the extent that the test sample is representative of production units.

Tested in accordance with the applicable sections of IES LM-79-19. Format of reports and angular increments based on IES LM-41-20 and LM-46-20.

The luminous intensity values, and other derived quantities, contained in this report are based on the absolute data, as measured.

Prorating the performance of the sample for the use of other component combinations (such as lamp / LED / Ballast / driver), or for use in different environmental conditions than that tested, may produce erroneous results.

This report is free of erasures and corrections.

Photometric intensity values are reported using the CIE C-Gamma coordinate system as defined in CIE publication number 121.

This report may contain data that are not covered by the NVLAP accreditation. Quantities marked with ‡ are not covered.

This report must not be used by the customer to claim product certification, approval or endorsement by NVLAP, NIST, or any agency of the Federal Government.