



Southwire™

INSULATED METALLIC GROUNDING BUSHINGS WITH ALUMINUM LUG - 105°C THERMOPLASTIC LINER - MALLEABLE IRON

FEATURES

- Liner is rated flame retardant to 105°C
- UL listed for use with copper or aluminum grounding conductor

APPLICATIONS

- Indoor or outdoor use (aluminum lug)
- Use with locknut to terminate service conduit to a cabinet
- Lug provided for bonding jumper to a neutral bus bar
- Round surface of bushing prevents damage to wire insulation
- Plastic liner prevents damage to wire insulation

STANDARD MATERIAL


- Body - Malleable iron
- Plastic insulator
- Lug - Aluminum
- Clamping screw - Steel
- Set screws - Steel



321M



PART #	SIZE	GROUNDING LUG WIRE SIZE		INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B
		MIN.	MAX.					
321M	1/2"	14	4	50	500	25	1.25"	.50"
322M	3/4"	14	4	50	500	30	1.48"	.54"
323M	1"	14	4	25	250	23	1.80"	.65"
324M	1-1/4"	14	4	20	200	34	2.40"	.73"
325M	1-1/2"	14	2	25	250	53	2.50"	.80"
326M	2"	14	2	25	250	78	3.03"	.80"
327M	2-1/2"	14	1/0	---	10	4	3.60"	.95"
328M	3"	14	1/0	---	10	5	4.16"	1.03"
329M	3-1/2"	14	2/0	---	10	15	4.75"	1.15"
330M	4"	14	2/0	---	10	20	5.30"	1.17"
330AM	5"	6	250MCM	---	10	25	6.15"	1.13"
330BM	6"	6	250MCM	---	10	35	7.19"	1.13"



Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.