


SUMNER*

SERIES 2000 MATERIAL LIFT

Built for heavy material and continuous work.

STANDARD FEATURES

- Lifts up to 1,000 lbs (455 kg)
- 10' (3.5 m), 15' (4.9 m), 20' (6.3 m), and 25' (7.7 m) heights
- No tools required
- No loose hardware
- Mast hold-down secures mast for safe transport
- Fits through doorways



PART #	DESCRIPTION	MAX HEIGHT	LIFTING CAPACITY	LIFT WEIGHT	SHIPPING WEIGHT
783700	2010 Material Lift	11' 7-1/8" (3.5 m)	1,000 lbs (455 kg)	188 lbs (85.5 kg)	223 lbs (104.4)
783701	2015 Material Lift	16' 2-1/2" (4.9 m)	800 lbs (360 kg)	280 lbs (127.3 kg)	315 lbs (143.2 kg)
783702	2020 Material Lift	20' 9-3/4" (6.3 m)	800 lbs (360 kg)	355 lbs (161.4 kg)	390 lbs (211.4 kg)
783703	2025 Material Lift	25' 5-1/8" (7.7 m)	650 lbs (300 kg)	430 lbs (195.5 kg)	465 lbs (211.4 kg)
783777	2010 Material Lift, Galvanized	11' 7-1/8" (3.5 m)	1,000 lbs (455 kg)	188 lbs (85.5 kg)	223 lbs (104.4)
783778	2015 Material Lift, Galvanized	16' 2-1/2" (4.9 m)	800 lbs (360 kg)	280 lbs (127.3 kg)	315 lbs (143.2 kg)
783779	2020 Material Lift, Galvanized	20' 9-3/4" (6.3 m)	800 lbs (360 kg)	355 lbs (161.4 kg)	390 lbs (211.4 kg)
783780	2025 Material Lift, Galvanized	25' 5-1/8" (7.7 m)	650 lbs (300 kg)	430 lbs (195.5 kg)	465 lbs (211.4 kg)

SERIES 2000 MATERIAL LIFT ACCESSORIES



PIPE CRADLE (#783705)

- Great for duct pipe or other HVAC applications
- Slides over standard forks



FORK EXTENSIONS (#783691)

- Push-button operation
- Extend forks from 28" - 42" (71-106cm)
- Longer forks decreases weight capacity to 200 lbs (90 kg)
(Clearly displayed on the forks when extended)



BOOM CARRIAGE (#783642)

- Ideal for installing pipe or other lifting applications
- Attached with four plunger pins
- 40" (100 cm) reach
- Five (5) hooking options
- Load capacity decreases the farther boom is extended, from 650 to 200 lbs (300 kg to 90 kg)

STEERING HANDLE (#786695)

Optional steering handle improves maneuverability of lift. With a push of a release button, handle folds out of the operator's way.

PART #	HEIGHT STOWED	LENGTH STOWED	HEIGHT OPERATING	LENGTH OPERATING	BASE WIDTH	WIDTH W/ STABILIZER LEGS	GROUND CLEARANCE	LOAD HEIGHT (MINIMUM)	MAX HEIGHT (FORKS DOWN)	MAX HEIGHT (FORKS REVERSED)
2010	6' 4" (1.93 m)	34" (0.86 m)	6'4" (1.93m)	5'2" (1.57m)	31-1/4" (0.80 m)	6' 2" (1.86 m)	2-1/2" (6.4 cm)	6" (15.2 cm)	9' 7-1/2" (2.9 m)	11' 7-1/8" (3.5 m)
2015	6' 4" (1.93 m)	34" (0.86 m)	6'4" (1.93m)	5'2" (1.57m)	31-1/4" (0.80 m)	6' 2" (1.86 m)	2-1/2" (6.4 cm)	6" (15.2 cm)	14' 2-3/4" (4.3 m)	16' 2-1/2" (4.9 m)
2020	6' 4" (1.93 m)	34" (0.86 m)	6'4" (1.93m)	6'1" (1.84 m)	31-1/4" (0.80 m)	6' 2" (1.86 m)	2-1/2" (6.4 cm)	6" (15.2 cm)	18' 10" (5.7 m)	20' 9-3/4" (6.3 m)
2025	6' 4" (1.93 m)	34" (0.86 m)	6'4" (1.93m)	6'1" (1.84 m)	31-1/4" (0.80 m)	6' 2" (1.86 m)	2-1/2" (6.4 cm)	6" (15.2 cm)	23' 5-3/8" (7.1 m)	25' 5-1/8" (7.7 m)