

-20°C to +60°C, 150 Volts Rated, UL ULEC and CSA LVLL



- APPLICATIONS**
- Outdoor Low-Voltage Underground Landscape Lighting Cable is designed for landscape, security, and outdoor accent lighting applications that not to exceed 150 volts.
  - Landscape Lighting Cable is Sunlight Resistant suitable for Direct Burial Stranded Copper Conductor Black PVC Insulation/Jacket.
- CONSTRUCTION**
- Two fully annealed bare stranded copper conductors
  - Insulation/Jacket: Premium-grade PVC -20°C to +60°C
  - Final assembly: Insulated/Jacketed conductors duplexed in a flat construction for easy tear-down during installation
  - Color: Black is standard Available in white or brown, but subject to minimum order quantity
- STANDARDS**
- Meets UL Subj 1493 cUL standards C22.2 35, CSA class 5834-01  
 UL Underground Low-Energy Circuit Cable for Outdoor Lighting  
 C(UL) Low-Voltage Landscape Lighting (LVLL)  
 EU RoHS Directive  
 Legend: XX AWG X/C UNDERGROUND LOW ENERGY CIRCUIT CABLE SUNLIGHT RESISTANT 60C 150V (UL) CSA LVLL 60C 30V FT1, FT2



Stock #	DESCRIPTION	AWG	#COND	NOM. OVERALL DIA. (Inches)	WEIGHT (Lb/Mft)
552131	LNDSKP LGHT 16/2 STR CU BK	16	2	0.156 × 0.307	41
552132	LNDSKP LGHT 14/2 STR CU BK	14	2	0.166 × 0.341	55
552134	LNDSKP LGHT 12/2 STR CU BK	12	2	0.186 × 0.37	69
552135	LNDSKP LGHT 10/2 STR CU BK	10	2	0.205 × 0.405	107
552136	LNDSKP LGHT 8/2 STR CU BK	8	2	0.27 × 0.53	163