



# Southwire™

## RIGID CONDUIT BODIES

### THREADED T TYPE - MALLEABLE IRON

#### FEATURES

- NPT tapered hubs
- Suitable for use in concrete

#### APPLICATION

- Provides access to conductors for maintenance and future system changes

#### STANDARD MATERIAL

- Malleable iron

#### STANDARD FINISH


- Zinc plated, aluminum enameled

#### CERTIFICATIONS

- UL Standard: UL 514A
- Fed. Spec: W-C-586D
- NEMA: FB 1



T1M



PART #	SIZE	WIRE SIZE		INTERNAL VOLUME (IN <sup>3</sup> )	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B	C
		MAX. NUMBER	MAX. SIZE						
T1M	1/2"	---	---	6	10	8	5.35"	1.31"	2.02"
T2M	3/4"	3	6 AWG	9.5	10	12	6"	1.62"	2.22"
T3M	1"	3	4 AWG	15	5	9	7.06"	1.88"	2.56"
T4M	1-1/4"	3	2 AWG	33	5	16	7.25"	2.50"	3.50"
T5M	1-1/2"	3	1 AWG	36	2	7	9.25"	2.67"	3.50"
T6M	2"	3	2/0 AWG	75	1	6	11.50"	3.29"	4.25"
T7M	2-1/2"	3	4/0 AWG	138	1	12	15"	3.9375"	5.718"
T8M	3"	3	4/0 AWG	170	1	15	15.125"	4.75"	8.875"
T9M	3-1/2"	3	350 MCM	300	1	23	18.125"	5.2031"	6.812"
T10M	4"	3	350 MCM	328	1	24	18.125"	5.5625"	7.203"

Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.