



RIGID LOCKNUTS

STEEL

FEATURES

- Tightens without deformation

APPLICATIONS

- To connect externally threaded conduit or connector to a threadless opening in a box or enclosure

STANDARD MATERIAL

- Steel


STANDARD FINISH

- Zinc plated



282

PART #	SIZE	THREADS PER INCH	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B	THREAD PITCH DIAMETER
281	1/2"	14	100	2000	20	1.15"	.11"	.787 – .797
282	3/4"	14	100	1000	20	1.45"	.115"	.999 – 1.009
283	1"	11-1/2	100	1000	30	1.75"	.14"	1.25 – 1.26
284	1-1/4"	11-1/2	50	500	20	2.10"	.14"	1.595 – 1.605
285	1-1/2"	11-1/2	50	500	30	2.40"	.14"	1.837 – 1.847
286	2"	11-1/2	25	250	20	2.95"	.14"	2.307 – 2.317
287	2-1/2"	8	---	50	6	3.55"	.185"	2.777 – 2.788
288TZ	3"	8	---	50	9	3.55"	.19"	3.403 – 3.414
289	3-1/2"	8	---	25	6	4.20"	.19"	3.892 – 3.904
290TZ	4"	8	---	25	7	4.75"	.19"	4.399 – 4.411
290A	5"	8	---	10	5	6.67"	.38"	5.488 – 5.50
290B	6"	8	---	10	8	7.93"	.40"	6.545 – 6.557



Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.