



Southwire™

4" OCTAGON BRACKETED BOXES

2-1/8" DEEP - DRAWN, FIXTURE EARS 3-1/2" ON CENTER
FOR CEILING FAN & FIXTURE SUPPORT

FEATURES

- Mounting hardware included
- 54171-FANNBWP has tight knockouts and gasket for weatherproof installations

APPLICATIONS

- Brace mounted ceiling fan rated boxes are mounted between joists to support ceiling fans or heavy light fixtures

STANDARD MATERIAL


- Galvanized steel

CERTIFICATIONS

- UL Listed



54171-FAN



54171-FANWP



54171-FANNB



LISTED

PART #	DESCRIPTION	RECOMMENDED MAX LOAD RATINGS		BRACKET TYPE	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
		CEILING FAN (DYNAMIC) LBS.	FIXTURE (STATIC) LBS.		SIDE CONDUIT	BOTTOM CONDUIT		
54171-FAN	CEILING FAN/LIGHT FIXTURE SUPPORT	70	150	FB	(3) 1/2"	(3) 1/2" & (2) 3/4"	20.0 (327.8)	25
54171-FANDR	CEILING FAN/FIXTURE SUPPORT, DEEP REVEAL	70	150	FB	(3) 1/2"	(5) 1/2"	20.0 (327.8)	25
54171-FANWP	WEATHERPROOF, CEILING FAN/LIGHT FIXTURE SUPPORT, WITH GROUND WIRE	70	150	FB	(3) 1/2"	(5) 1/2"	20.0 (327.8)	25
54171-FANNB	CEILING FAN/LIGHT FIXTURE SUPPORT	70	150	N/A	4 (1/2")	5 (1/2")	20.0 (327.8)	25

Rev. 2, 11/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.