



Southwire™

INSULATED BONDING BUSHINGS

CORROSION RESISTANT - MALLEABLE IRON

FEATURES

- Hot dip galvanized for superior protection against corrosion
- Tin plated copper lay-in lug
- UV Resistant liner for direct exposure to the sun
- Stainless steel hardware

APPLICATIONS

- Ideal for solar photovoltaic applications.
- Use to provide a means of grounding Rigid or IMC conduit
- Indoor or outdoor use (lay-in lug)
- Use lug provided for bonding jumper to a neutral bus bar
- Prevent damage to wire insulation with the UV resistant liner

STANDARD MATERIAL


- Body – Malleable iron
- Lug – Tin plated copper
- Clamping screw – Stainless steel
- Set screws – Stainless steel

STANDARD MATERIAL

- Hot dip galvanized



332MSL



PART #	SIZE	GROUNDING LUG WIRE SIZE		INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	RECOMMENDED TORQUE (IN - LBS)	A	B
		MIN.	MAX.						
332MSL	3/4"	14	4	10	100	14	35	1.31"	.57"
333MSL	1"	14	4	5	50	9	35	1.61"	.65"
334MSL	1-1/4"	14	4	5	50	10	35	1.91"	.71"
335MSL	1-1/2"	14	4	5	50	12	35	2.16"	.73"
336MSL	2"	14	4	5	50	15	35	2.72"	.73"
334AMSL	1-1/4"	14	2/0	5	50	16	35	1.91"	.71"
335AMSL	1-1/2"	14	2/0	5	50	17	35	2.16"	.73"
336AMSL	2"	14	2/0	5	50	20	35	2.72"	.73"

Rev. 0, 06/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.